

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291740

Luminaire Tested: P3AS09R15W2N902765DE010 E3DL1GPH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1291740  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R15W2N902765DE010 E3DL1GPH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3500K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 301.0 lumens  
Efficiency: N/A  
Efficacy: 33.4 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1291740  
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DL1GPH\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1291740  
 CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DL1GPH\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	110	106	103	100	108	104	101	99	101	99	97	98	96	95	96	94	93	91
3	106	101	97	93	104	99	96	93	97	94	91	94	92	90	92	90	88	87
4	102	96	92	88	100	95	91	88	93	89	87	91	88	86	89	87	85	83
5	98	92	87	84	97	91	87	83	89	85	83	88	84	82	86	83	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77
7	92	85	80	77	91	84	80	76	83	79	76	82	78	76	81	78	75	74
8	89	81	77	74	88	81	77	73	80	76	73	79	75	73	78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69
10	84	76	71	68	83	76	71	68	75	71	68	74	71	68	74	70	68	67

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	257129
5°	228241
10°	158514
15°	93735
20°	53391
25°	30510
30°	16889
35°	8994
40°	4981
45°	2698
50°	1672
55°	1338
60°	1140
65°	1038
70°	898
75°	1017
80°	758
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2698 cd/sqm



TEST NUMBER: P1291740  
 CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DL1GPH\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.2	29.3
10°-20°	116.4	38.7
20°-30°	59.9	19.9
30°-40°	22.5	7.5
40°-50°	7.4	2.4
50°-60°	3.2	1.1
60°-70°	2.0	0.7
70°-80°	1.2	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	264.5	87.9
0°-40°	287.0	95.3
0°-60°	297.5	98.8
0°-90°	301.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	301.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1173	
5°	1037	88
15°	413	116
25°	126	60
35°	34	23
45°	9	7
55°	4	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1291740  
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DL1GPH\_3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1172.6
1°	1170.3
2°	1154.9
3°	1125.6
4°	1087.1
5°	1036.9
6°	980.1
7°	917.7
8°	848.4
9°	780.0
10°	711.9
12.5°	547.7
15°	412.9
17.5°	309.1
20°	228.8
22.5°	170.8
25°	126.1
27.5°	91.9
30°	66.7
32.5°	47.3
35°	33.6
37.5°	24.1
40°	17.4
42.5°	12.5
45°	8.7
47.5°	6.4
50°	4.9
52.5°	4.1
55°	3.5
57.5°	2.9
60°	2.6
62.5°	2.3
65°	2.0
67.5°	1.7
70°	1.4
72.5°	1.4
75°	1.2
77.5°	0.9
80°	0.6
82.5°	0.6
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)