

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291779

Luminaire Tested: P3AS09R15W2N902765DE010 E3DLD1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291779
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R15W2N902765DE010 E3DLD1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 6500K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 228.0 lumens
Efficiency: N/A
Efficacy: 25.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291779
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1GPH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1291779
 CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1GPH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93		91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85		83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78		76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72		70
5	89	80	73	68	87	79	73	68	77	72	67	75	70	67	74	69	66		65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61		60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57		56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53		52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50		49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47		46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	57517
5°	55954
10°	51124
15°	44790
20°	38410
25°	32082
30°	25675
35°	19247
40°	13969
45°	9148
50°	5731
55°	3861
60°	3421
65°	3165
70°	2949
75°	2711
80°	2526
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9148 cd/sqm



TEST NUMBER: P1291779

CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.5	10.3
10°-20°	55.0	24.1
20°-30°	60.6	26.6
30°-40°	45.4	19.9
40°-50°	23.5	10.3
50°-60°	9.8	4.3
60°-70°	6.0	2.6
70°-80°	3.4	1.5
80°-90°	1.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	139.0	61.0
0°-40°	184.3	80.8
0°-60°	217.6	95.4
0°-90°	228.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	228.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	262	
5°	254	23
15°	197	55
25°	133	61
35°	72	45
45°	30	24
55°	10	10
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1291779
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1GPH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	262.3
1°	262.6
2°	261.7
3°	260.0
4°	257.4
5°	254.2
6°	250.1
7°	245.8
8°	240.6
9°	235.1
10°	229.6
12.5°	213.7
15°	197.3
17.5°	180.8
20°	164.6
22.5°	148.2
25°	132.6
27.5°	117.0
30°	101.4
32.5°	86.1
35°	71.9
37.5°	59.8
40°	48.8
42.5°	38.7
45°	29.5
47.5°	22.2
50°	16.8
52.5°	12.4
55°	10.1
57.5°	9.0
60°	7.8
62.5°	6.9
65°	6.1
67.5°	5.2
70°	4.6
72.5°	3.8
75°	3.2
77.5°	2.6
80°	2.0
82.5°	1.4
85°	0.9
87.5°	0.3
90°	0.0

(END OF REPORT)