

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291799

Luminaire Tested: P3AS09R15W2N902765DE010 E3DLD1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291799
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R15W2N902765DE010 E3DLD1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 460.0 lumens
Efficiency: N/A
Efficacy: 51.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291799
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1291799

CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83			
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65			
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60			
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56			
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52			
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49			
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	116021
5°	112877
10°	103160
15°	90352
20°	77520
25°	64721
30°	51780
35°	38842
40°	28196
45°	18421
50°	11531
55°	7799
60°	6885
65°	6330
70°	5963
75°	5422
80°	5177
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18421 cd/sqm



TEST NUMBER: P1291799
 CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.3	10.3
10°-20°	110.9	24.1
20°-30°	122.2	26.6
30°-40°	91.5	19.9
40°-50°	47.4	10.3
50°-60°	19.7	4.3
60°-70°	12.2	2.6
70°-80°	6.8	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	280.4	61.0
0°-40°	371.9	80.9
0°-60°	439.0	95.4
0°-90°	460.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	460.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	529	
5°	513	47
15°	398	111
25°	268	122
35°	145	92
45°	59	47
55°	20	20
65°	12	12
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1291799
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	529.1
1°	529.7
2°	528.0
3°	524.5
4°	519.2
5°	512.8
6°	504.7
7°	495.9
8°	485.4
9°	474.4
10°	463.3
12.5°	431.2
15°	398.0
17.5°	364.8
20°	332.2
22.5°	298.9
25°	267.5
27.5°	236.0
30°	204.5
32.5°	173.7
35°	145.1
37.5°	120.6
40°	98.5
42.5°	78.1
45°	59.4
47.5°	44.9
50°	33.8
52.5°	25.1
55°	20.4
57.5°	18.1
60°	15.7
62.5°	14.0
65°	12.2
67.5°	10.5
70°	9.3
72.5°	7.6
75°	6.4
77.5°	5.2
80°	4.1
82.5°	2.9
85°	1.7
87.5°	0.6
90°	0.0

(END OF REPORT)