

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291800

Luminaire Tested: P3AS09R15W2N902765DE010 E3DLD1WH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291800
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R15W2N902765DE010 E3DLD1WH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3500K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 467.0 lumens
Efficiency: N/A
Efficacy: 51.9 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291800
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1WH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1291800
 CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1WH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91	91	91	91
2	106	100	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83	83	83	83
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76	76	76	76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70	70	70	70
5	89	80	73	68	87	79	73	68	77	72	67	75	71	67	74	69	66	65	65	65	65
6	84	74	68	63	83	73	67	63	72	66	62	70	66	62	69	65	61	60	60	60	60
7	80	69	63	58	78	69	63	58	67	62	58	66	61	57	65	61	57	56	56	56	56
8	76	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	117798
5°	114594
10°	104719
15°	91737
20°	78687
25°	65713
30°	52590
35°	39431
40°	28625
45°	18700
50°	11701
55°	7914
60°	7017
65°	6434
70°	6091
75°	5507
80°	5177
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18700 cd/sqm



TEST NUMBER: P1291800
 CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1WH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.0	10.3
10°-20°	112.6	24.1
20°-30°	124.1	26.6
30°-40°	92.9	19.9
40°-50°	48.2	10.3
50°-60°	19.9	4.3
60°-70°	12.4	2.6
70°-80°	6.9	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	284.7	61.0
0°-40°	377.6	80.9
0°-60°	445.7	95.4
0°-90°	467.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	467.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	537	
5°	521	48
15°	404	113
25°	272	124
35°	147	93
45°	60	48
55°	21	20
65°	12	12
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1291800
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1WH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	537.2
1°	537.8
2°	536.0
3°	532.5
4°	527.1
5°	520.6
6°	512.3
7°	503.5
8°	492.8
9°	481.6
10°	470.3
12.5°	437.8
15°	404.1
17.5°	370.4
20°	337.2
22.5°	303.5
25°	271.6
27.5°	239.6
30°	207.7
32.5°	176.3
35°	147.3
37.5°	122.5
40°	100.0
42.5°	79.3
45°	60.3
47.5°	45.6
50°	34.3
52.5°	25.4
55°	20.7
57.5°	18.3
60°	16.0
62.5°	14.2
65°	12.4
67.5°	10.6
70°	9.5
72.5°	7.7
75°	6.5
77.5°	5.3
80°	4.1
82.5°	3.0
85°	1.8
87.5°	0.6
90°	0.0

(END OF REPORT)