

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289445

Luminaire Tested: P3AS05R40W2N902750DE010 E3DL1WH\_4000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1289445  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R40W2N902750DE010 E3DL1WH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 4000K CCT AND, 90CRI ,  
E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 294.9 lumens  
Efficiency: N/A  
Efficacy: 50.0 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1289445

CATALOG NUMBER: P3AS05R40W2N902750DE010 E3DL1WH\_4000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1289445

CATALOG NUMBER: P3AS05R40W2N902750DE010 E3DL1WH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 96  | 95  | 93  |    |    |
| 2   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 94  | 97  | 94  | 91  | 94  | 92  | 89  | 92  | 89  | 88  | 86  |    |    |
| 3   | 102 | 95  | 90  | 86  | 100 | 94  | 89  | 85  | 91  | 87  | 84  | 89  | 85  | 83  | 86  | 84  | 81  | 80  |    |    |
| 4   | 97  | 89  | 83  | 79  | 95  | 88  | 83  | 79  | 86  | 81  | 78  | 84  | 80  | 77  | 82  | 79  | 76  | 74  |    |    |
| 5   | 92  | 83  | 77  | 73  | 90  | 82  | 77  | 73  | 81  | 76  | 72  | 79  | 75  | 72  | 77  | 74  | 71  | 69  |    |    |
| 6   | 87  | 78  | 72  | 68  | 86  | 78  | 72  | 68  | 76  | 71  | 67  | 75  | 70  | 67  | 73  | 70  | 66  | 65  |    |    |
| 7   | 83  | 74  | 68  | 64  | 82  | 73  | 68  | 64  | 72  | 67  | 63  | 71  | 66  | 63  | 70  | 66  | 62  | 61  |    |    |
| 8   | 79  | 70  | 64  | 60  | 78  | 69  | 64  | 60  | 68  | 63  | 59  | 67  | 63  | 59  | 66  | 62  | 59  | 58  |    |    |
| 9   | 76  | 66  | 60  | 56  | 75  | 66  | 60  | 56  | 65  | 60  | 56  | 64  | 59  | 56  | 63  | 59  | 56  | 54  |    |    |
| 10  | 72  | 63  | 57  | 53  | 71  | 62  | 57  | 53  | 62  | 57  | 53  | 61  | 56  | 53  | 60  | 56  | 53  | 51  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 91857 |
| 5°  | 90006 |
| 10° | 83788 |
| 15° | 73031 |
| 20° | 58852 |
| 25° | 44107 |
| 30° | 31017 |
| 35° | 20318 |
| 40° | 12309 |
| 45° | 7350  |
| 50° | 4401  |
| 55° | 3517  |
| 60° | 3158  |
| 65° | 2698  |
| 70° | 2565  |
| 75° | 2033  |
| 80° | 2020  |
| 85° | 2013  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 7350 cd/sqm

TEST NUMBER: P1289445

CATALOG NUMBER: P3AS05R40W2N902750DE010 E3DL1WH\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 38.0   | 12.9      |
| 10°-20°   | 88.6   | 30.0      |
| 20°-30°   | 83.5   | 28.3      |
| 30°-40°   | 48.3   | 16.4      |
| 40°-50°   | 19.2   | 6.5       |
| 50°-60°   | 8.5    | 2.9       |
| 60°-70°   | 5.2    | 1.8       |
| 70°-80°   | 2.7    | 0.9       |
| 80°-90°   | 0.9    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 210.1  | 71.2      |
| 0°-40°    | 258.3  | 87.6      |
| 0°-60°    | 286.1  | 97.0      |
| 0°-90°    | 294.9  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 294.9  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 419 |      |
| 5°  | 409 | 38   |
| 15° | 322 | 89   |
| 25° | 182 | 83   |
| 35° | 76  | 48   |
| 45° | 24  | 19   |
| 55° | 9   | 8    |
| 65° | 5   | 5    |
| 75° | 2   | 3    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1289445

CATALOG NUMBER: P3AS05R40W2N902750DE010 E3DL1WH\_4000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 418.9 |
| 2.5°  | 416.5 |
| 5°    | 408.9 |
| 7.5°  | 394.8 |
| 10°   | 376.3 |
| 12.5° | 351.4 |
| 15°   | 321.7 |
| 17.5° | 288.4 |
| 20°   | 252.2 |
| 22.5° | 216.1 |
| 25°   | 182.3 |
| 27.5° | 151.0 |
| 30°   | 122.5 |
| 32.5° | 97.6  |
| 35°   | 75.9  |
| 37.5° | 57.4  |
| 40°   | 43.0  |
| 42.5° | 32.1  |
| 45°   | 23.7  |
| 47.5° | 17.3  |
| 50°   | 12.9  |
| 52.5° | 10.4  |
| 55°   | 9.2   |
| 57.5° | 8.4   |
| 60°   | 7.2   |
| 62.5° | 6.0   |
| 65°   | 5.2   |
| 67.5° | 4.4   |
| 70°   | 4.0   |
| 72.5° | 3.2   |
| 75°   | 2.4   |
| 77.5° | 2.0   |
| 80°   | 1.6   |
| 82.5° | 1.2   |
| 85°   | 0.8   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)