

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289481

Luminaire Tested: P3AS05R40W2N902750DE010 E3DLD1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289481
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R40W2N902750DE010 E3DLD1WMH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 357.0 lumens
Efficiency: N/A
Efficacy: 60.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289481

CATALOG NUMBER: P3AS05R40W2N902750DE010 E3DLD1WMH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1289481

CATALOG NUMBER: P3AS05R40W2N902750DE010 E3DLD1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69		
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59		
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55		
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51		
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48		
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	80147
5°	78692
10°	74169
15°	67378
20°	59178
25°	50543
30°	41880
35°	32284
40°	22986
45°	15474
50°	8460
55°	5964
60°	5614
65°	5189
70°	4616
75°	4406
80°	3536
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15474 cd/sqm

TEST NUMBER: P1289481

CATALOG NUMBER: P3AS05R40W2N902750DE010 E3DLD1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.3	9.3
10°-20°	82.7	23.2
20°-30°	95.6	26.8
30°-40°	75.3	21.1
40°-50°	38.6	10.8
50°-60°	14.8	4.1
60°-70°	9.8	2.7
70°-80°	5.3	1.5
80°-90°	1.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	211.6	59.3
0°-40°	286.9	80.4
0°-60°	340.4	95.3
0°-90°	357.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	357.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	366	
5°	358	33
15°	297	83
25°	209	96
35°	121	75
45°	50	39
55°	16	15
65°	10	10
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P1289481

CATALOG NUMBER: P3AS05R40W2N902750DE010 E3DLD1WMH_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	365.5
2.5°	363.5
5°	357.5
7.5°	347.1
10°	333.1
12.5°	316.7
15°	296.8
17.5°	276.0
20°	253.6
22.5°	230.9
25°	208.9
27.5°	186.9
30°	165.4
32.5°	143.4
35°	120.6
37.5°	99.5
40°	80.3
42.5°	63.9
45°	49.9
47.5°	36.3
50°	24.8
52.5°	18.0
55°	15.6
57.5°	14.0
60°	12.8
62.5°	11.2
65°	10.0
67.5°	8.4
70°	7.2
72.5°	6.0
75°	5.2
77.5°	4.0
80°	2.8
82.5°	2.4
85°	1.2
87.5°	0.8
90°	0.0

(END OF REPORT)