

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291948

Luminaire Tested: P3AS09R20W2N902750DE010 E3DLD1GPH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1291948  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R20W2N902750DE010 E3DLD1GPH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 5000K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 227.0 lumens  
Efficiency: N/A  
Efficacy: 25.2 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1291948  
CATALOG NUMBER: P3AS09R20W2N902750DE010 E3DLD1GPH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1291948

CATALOG NUMBER: P3AS09R20W2N902750DE010 E3DLD1GPH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83			83
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76			76
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70			70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65			65
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60			60
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55			55
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52			52
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48			48
10	68	58	51	47	67	57	51	47	56	51	47	56	51	47	55	50	47	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	56158
5°	54655
10°	50277
15°	44245
20°	37943
25°	31889
30°	25776
35°	19595
40°	13940
45°	9210
50°	5697
55°	3747
60°	3421
65°	3165
70°	2949
75°	2711
80°	2526
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9210 cd/sqm



TEST NUMBER: P1291948

CATALOG NUMBER: P3AS09R20W2N902750DE010 E3DLD1GPH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	23.0	10.1
10°-20°	54.3	23.9
20°-30°	60.2	26.5
30°-40°	45.9	20.2
40°-50°	23.5	10.4
50°-60°	9.7	4.3
60°-70°	6.0	2.7
70°-80°	3.4	1.5
80°-90°	1.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	137.5	60.6
0°-40°	183.4	80.8
0°-60°	216.6	95.4
0°-90°	227.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	227.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	256	
5°	248	23
15°	195	54
25°	132	60
35°	73	46
45°	30	24
55°	10	10
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1291948  
CATALOG NUMBER: P3AS09R20W2N902750DE010 E3DLD1GPH\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	256.1
1°	256.3
2°	255.2
3°	253.8
4°	251.4
5°	248.3
6°	244.5
7°	240.5
8°	236.2
9°	231.0
10°	225.8
12.5°	210.8
15°	194.9
17.5°	178.8
20°	162.6
22.5°	146.5
25°	131.8
27.5°	117.1
30°	101.8
32.5°	87.4
35°	73.2
37.5°	60.8
40°	48.7
42.5°	38.4
45°	29.7
47.5°	22.5
50°	16.7
52.5°	12.4
55°	9.8
57.5°	8.9
60°	7.8
62.5°	6.9
65°	6.1
67.5°	5.2
70°	4.6
72.5°	3.7
75°	3.2
77.5°	2.6
80°	2.0
82.5°	1.4
85°	0.9
87.5°	0.3
90°	0.0

(END OF REPORT)