

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289654

Luminaire Tested: P3AS05R40W2N902765DE010 E3DLP1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289654
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R40W2N902765DE010 E3DLP1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 144.0 lumens
Efficiency: N/A
Efficacy: 24.4 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289654

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DLP1GPH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1289654

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DLP1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95		93
2	107	102	98	95	105	101	97	93	97	94	91		94	92	89		92	89	88		86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86	84	81		80
4	97	89	83	79	95	88	83	79	86	81	78		84	80	77		82	79	76		74
5	92	83	77	73	90	82	77	73	81	76	72		79	75	71		77	74	71		69
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73	69	66		65
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70	66	62		61
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66	62	59		58
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63	59	56		54
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44843
5°	43936
10°	40903
15°	35642
20°	28726
25°	21534
30°	15142
35°	9931
40°	6011
45°	3597
50°	2149
55°	1720
60°	1535
65°	1297
70°	1282
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3597 cd/sqm

TEST NUMBER: P1289654

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DLP1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.5	12.9
10°-20°	43.2	30.0
20°-30°	40.8	28.3
30°-40°	23.6	16.4
40°-50°	9.4	6.5
50°-60°	4.2	2.9
60°-70°	2.6	1.8
70°-80°	1.4	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	102.5	71.2
0°-40°	126.1	87.6
0°-60°	139.7	97.0
0°-90°	144.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	144.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	204	
5°	200	19
15°	157	43
25°	89	41
35°	37	24
45°	12	9
55°	4	4
65°	2	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1289654

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DLP1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	204.5
2.5°	203.3
5°	199.6
7.5°	192.7
10°	183.7
12.5°	171.5
15°	157.0
17.5°	140.8
20°	123.1
22.5°	105.5
25°	89.0
27.5°	73.7
30°	59.8
32.5°	47.6
35°	37.1
37.5°	28.0
40°	21.0
42.5°	15.7
45°	11.6
47.5°	8.4
50°	6.3
52.5°	5.1
55°	4.5
57.5°	4.1
60°	3.5
62.5°	2.9
65°	2.5
67.5°	2.2
70°	2.0
72.5°	1.6
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)