

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291984

Luminaire Tested: P3AS09R20W2N902750DE010 E3PHLD1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291984
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R20W2N902750DE010 E3PHLD1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 364.0 lumens
Efficiency: N/A
Efficacy: 40.4 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291984
CATALOG NUMBER: P3AS09R20W2N902750DE010 E3PHLD1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1291984

CATALOG NUMBER: P3AS09R20W2N902750DE010 E3PHLD1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	85	82	80
3	98	90	83	78	95	88	82	78	85	81	77	83	79	75	80	77	74	72
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	81	70	63	58	79	70	63	58	68	62	58	66	61	57	65	60	57	55
7	76	66	59	54	75	65	58	53	63	58	53	62	57	53	61	56	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103237
5°	95906
10°	81205
15°	63564
20°	50031
25°	39873
30°	32081
35°	26154
40°	21612
45°	18234
50°	15624
55°	13419
60°	11710
65°	10273
70°	8784
75°	7795
80°	5809
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18234 cd/sqm



TEST NUMBER: P1291984

CATALOG NUMBER: P3AS09R20W2N902750DE010 E3PHLD1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.3	10.8
10°-20°	78.4	21.5
20°-30°	76.1	20.9
30°-40°	61.5	16.9
40°-50°	45.7	12.6
50°-60°	31.7	8.7
60°-70°	19.9	5.5
70°-80°	9.7	2.7
80°-90°	1.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	193.8	53.3
0°-40°	255.4	70.1
0°-60°	332.8	91.4
0°-90°	364.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	364.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	471	
5°	436	39
15°	280	78
25°	165	76
35°	98	62
45°	59	46
55°	35	32
65°	20	20
75°	9	10
85°	2	2
90°	0	



TEST NUMBER: P1291984
CATALOG NUMBER: P3AS09R20W2N902750DE010 E3PHLD1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	470.8
2.5°	460.1
5°	435.7
7.5°	402.9
10°	364.7
12.5°	322.7
15°	280.0
17.5°	244.9
20°	214.4
22.5°	187.7
25°	164.8
27.5°	145.0
30°	126.7
32.5°	111.4
35°	97.7
37.5°	85.5
40°	75.5
42.5°	66.4
45°	58.8
47.5°	51.9
50°	45.8
52.5°	40.4
55°	35.1
57.5°	30.5
60°	26.7
62.5°	23.7
65°	19.8
67.5°	16.8
70°	13.7
72.5°	11.4
75°	9.2
77.5°	6.9
80°	4.6
82.5°	2.3
85°	1.5
87.5°	0.0
90°	0.0

(END OF REPORT)