

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289724

Luminaire Tested: P3AS05R45W2N902750DE010 E3DL1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289724
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R45W2N902750DE010 E3DL1GPH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 220.1 lumens
Efficiency: N/A
Efficacy: 37.3 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289724

CATALOG NUMBER: P3AS05R45W2N902750DE010 E3DL1GPH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1289724

CATALOG NUMBER: P3AS05R45W2N902750DE010 E3DL1GPH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96		94
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93	91	90		88
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89	86	84		83
4	99	92	87	83	97	91	86	82	89	84	81		87	83	80		85	82	79		78
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81	78	75		74
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77	74	71		69
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67		66
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70	67	64		62
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67	63	61		59
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65	61	58		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	82625
5°	80673
10°	74169
15°	62838
20°	48748
25°	34091
30°	21472
35°	12635
40°	7156
45°	3473
50°	1194
55°	994
60°	965
65°	934
70°	898
75°	847
80°	758
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3473 cd/sqm

TEST NUMBER: P1289724

CATALOG NUMBER: P3AS05R45W2N902750DE010 E3DL1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.9	15.4
10°-20°	76.0	34.5
20°-30°	64.6	29.3
30°-40°	30.8	14.0
40°-50°	9.3	4.2
50°-60°	2.4	1.1
60°-70°	1.8	0.8
70°-80°	1.1	0.5
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	174.5	79.3
0°-40°	205.3	93.3
0°-60°	216.9	98.6
0°-90°	220.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	220.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	377	
5°	366	34
15°	277	76
25°	141	65
35°	47	31
45°	11	9
55°	3	2
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1289724

CATALOG NUMBER: P3AS05R45W2N902750DE010 E3DL1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	376.8
2.5°	374.4
5°	366.5
7.5°	353.0
10°	333.1
12.5°	306.7
15°	276.8
17.5°	243.6
20°	208.9
22.5°	173.7
25°	140.9
27.5°	111.0
30°	84.8
32.5°	63.7
35°	47.2
37.5°	34.8
40°	25.0
42.5°	17.3
45°	11.2
47.5°	6.3
50°	3.5
52.5°	2.8
55°	2.6
57.5°	2.4
60°	2.2
62.5°	2.0
65°	1.8
67.5°	1.6
70°	1.4
72.5°	1.2
75°	1.0
77.5°	0.8
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0

(END OF REPORT)