

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291988

Luminaire Tested: P3AS09R20W2N902750DE010 E3PHLD1MW_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291988
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R20W2N902750DE010 E3PHLD1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 5000K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 405.0 lumens
Efficiency: N/A
Efficacy: 45.0 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291988
CATALOG NUMBER: P3AS09R20W2N902750DE010 E3PHLD1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1291988

CATALOG NUMBER: P3AS09R20W2N902750DE010 E3PHLD1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	85	82	80
3	98	90	83	78	95	88	82	78	85	81	77	83	79	75	80	77	74	72
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	60
6	81	70	63	58	79	70	63	58	68	62	58	66	61	57	65	60	57	55
7	76	66	59	54	75	65	58	53	64	58	53	62	57	53	61	56	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44
10	65	54	48	43	64	54	48	43	53	47	43	52	47	43	51	46	43	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	114859
5°	106691
10°	90357
15°	70738
20°	55678
25°	44374
30°	35676
35°	29098
40°	24045
45°	20281
50°	17364
55°	14948
60°	13025
65°	11467
70°	9809
75°	8642
80°	6440
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20281 cd/sqm



TEST NUMBER: P1291988

CATALOG NUMBER: P3AS09R20W2N902750DE010 E3PHLD1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.8	10.8
10°-20°	87.2	21.5
20°-30°	84.7	20.9
30°-40°	68.4	16.9
40°-50°	50.9	12.6
50°-60°	35.3	8.7
60°-70°	22.1	5.5
70°-80°	10.7	2.6
80°-90°	1.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	215.7	53.3
0°-40°	284.1	70.1
0°-60°	370.3	91.4
0°-90°	405.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	405.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	524	
5°	485	44
15°	312	87
25°	183	85
35°	109	68
45°	65	51
55°	39	35
65°	22	22
75°	10	11
85°	2	2
90°	0	



TEST NUMBER: P1291988
CATALOG NUMBER: P3AS09R20W2N902750DE010 E3PHLD1MW_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	523.8
2.5°	511.9
5°	484.7
7.5°	448.2
10°	405.8
12.5°	359.1
15°	311.6
17.5°	272.5
20°	238.6
22.5°	208.8
25°	183.4
27.5°	161.3
30°	140.9
32.5°	123.9
35°	108.7
37.5°	95.1
40°	84.0
42.5°	73.9
45°	65.4
47.5°	57.7
50°	50.9
52.5°	45.0
55°	39.1
57.5°	34.0
60°	29.7
62.5°	26.3
65°	22.1
67.5°	18.7
70°	15.3
72.5°	12.7
75°	10.2
77.5°	7.6
80°	5.1
82.5°	2.5
85°	1.7
87.5°	0.0
90°	0.0

(END OF REPORT)