

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292138

Luminaire Tested: P3AS09R20W2N902765DE010 E3PHLD1MW\_2700K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292138  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R20W2N902765DE010 E3PHLD1MW\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI ,  
E3PHLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 364.0 lumens  
Efficiency: N/A  
Efficacy: 40.4 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292138  
CATALOG NUMBER: P3AS09R20W2N902765DE010 E3PHLD1MW\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1292138

CATALOG NUMBER: P3AS09R20W2N902765DE010 E3PHLD1MW\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1   | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 102 | 100 | 97  | 98  | 96  | 95  | 95  | 93  | 92  | 90  |
| 2   | 104 | 98  | 93  | 89  | 102 | 96  | 92  | 88  | 93  | 89  | 86  | 90  | 87  | 84  | 87  | 85  | 82  | 80  |
| 3   | 98  | 90  | 83  | 78  | 95  | 88  | 82  | 78  | 85  | 81  | 77  | 83  | 79  | 75  | 80  | 77  | 74  | 72  |
| 4   | 92  | 82  | 75  | 70  | 90  | 81  | 75  | 70  | 79  | 73  | 69  | 77  | 72  | 68  | 75  | 71  | 67  | 66  |
| 5   | 86  | 76  | 69  | 64  | 84  | 75  | 68  | 63  | 73  | 67  | 63  | 71  | 66  | 62  | 70  | 65  | 62  | 60  |
| 6   | 81  | 70  | 63  | 58  | 79  | 70  | 63  | 58  | 68  | 62  | 58  | 66  | 61  | 57  | 65  | 60  | 57  | 55  |
| 7   | 76  | 66  | 59  | 54  | 75  | 65  | 58  | 53  | 63  | 58  | 53  | 62  | 57  | 53  | 61  | 56  | 53  | 51  |
| 8   | 72  | 61  | 54  | 50  | 71  | 61  | 54  | 50  | 60  | 54  | 49  | 58  | 53  | 49  | 57  | 53  | 49  | 47  |
| 9   | 69  | 58  | 51  | 46  | 67  | 57  | 51  | 46  | 56  | 50  | 46  | 55  | 50  | 46  | 54  | 49  | 46  | 44  |
| 10  | 65  | 54  | 48  | 43  | 64  | 54  | 48  | 43  | 53  | 47  | 43  | 52  | 47  | 43  | 51  | 46  | 43  | 41  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 103237 |
| 5°  | 95906  |
| 10° | 81205  |
| 15° | 63564  |
| 20° | 50031  |
| 25° | 39873  |
| 30° | 32081  |
| 35° | 26154  |
| 40° | 21612  |
| 45° | 18234  |
| 50° | 15624  |
| 55° | 13419  |
| 60° | 11710  |
| 65° | 10273  |
| 70° | 8784   |
| 75° | 7795   |
| 80° | 5809   |
| 85° | 3774   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18234 cd/sqm



TEST NUMBER: P1292138

CATALOG NUMBER: P3AS09R20W2N902765DE010 E3PHLD1MW\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 39.3   | 10.8      |
| 10°-20°   | 78.4   | 21.5      |
| 20°-30°   | 76.1   | 20.9      |
| 30°-40°   | 61.5   | 16.9      |
| 40°-50°   | 45.7   | 12.6      |
| 50°-60°   | 31.7   | 8.7       |
| 60°-70°   | 19.9   | 5.5       |
| 70°-80°   | 9.7    | 2.7       |
| 80°-90°   | 1.7    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 193.8  | 53.3      |
| 0°-40°    | 255.4  | 70.1      |
| 0°-60°    | 332.8  | 91.4      |
| 0°-90°    | 364.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 364.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 471 |      |
| 5°  | 436 | 39   |
| 15° | 280 | 78   |
| 25° | 165 | 76   |
| 35° | 98  | 62   |
| 45° | 59  | 46   |
| 55° | 35  | 32   |
| 65° | 20  | 20   |
| 75° | 9   | 10   |
| 85° | 2   | 2    |
| 90° | 0   |      |



TEST NUMBER: P1292138  
CATALOG NUMBER: P3AS09R20W2N902765DE010 E3PHLD1MW\_2700K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 470.8 |
| 2.5°  | 460.1 |
| 5°    | 435.7 |
| 7.5°  | 402.9 |
| 10°   | 364.7 |
| 12.5° | 322.7 |
| 15°   | 280.0 |
| 17.5° | 244.9 |
| 20°   | 214.4 |
| 22.5° | 187.7 |
| 25°   | 164.8 |
| 27.5° | 145.0 |
| 30°   | 126.7 |
| 32.5° | 111.4 |
| 35°   | 97.7  |
| 37.5° | 85.5  |
| 40°   | 75.5  |
| 42.5° | 66.4  |
| 45°   | 58.8  |
| 47.5° | 51.9  |
| 50°   | 45.8  |
| 52.5° | 40.4  |
| 55°   | 35.1  |
| 57.5° | 30.5  |
| 60°   | 26.7  |
| 62.5° | 23.7  |
| 65°   | 19.8  |
| 67.5° | 16.8  |
| 70°   | 13.7  |
| 72.5° | 11.4  |
| 75°   | 9.2   |
| 77.5° | 6.9   |
| 80°   | 4.6   |
| 82.5° | 2.3   |
| 85°   | 1.5   |
| 87.5° | 0.0   |
| 90°   | 0.0   |

(END OF REPORT)