

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292205

Luminaire Tested: P3AS09R25W2N902750DE010 E3DL1GPH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292205  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R25W2N902750DE010 E3DL1GPH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 271.0 lumens  
Efficiency: N/A  
Efficacy: 30.1 lumens/watt  
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292205  
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DL1GPH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1292205  
 CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DL1GPH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	94
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	85	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	82	79
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	80	77
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	77	74
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	74	71
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	71	68
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	69	66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	173846
5°	162183
10°	129924
15°	88196
20°	53368
25°	31211
30°	17775
35°	9771
40°	5181
45°	2729
50°	1603
55°	1185
60°	1009
65°	1090
70°	1026
75°	847
80°	631
85°	755

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2729 cd/sqm



TEST NUMBER: P1292205

CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DL1GPH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.4	24.1
10°-20°	106.8	39.4
20°-30°	61.0	22.5
30°-40°	24.1	8.9
40°-50°	7.4	2.7
50°-60°	2.9	1.1
60°-70°	2.0	0.7
70°-80°	1.1	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	233.2	86.1
0°-40°	257.3	94.9
0°-60°	267.6	98.7
0°-90°	271.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	271.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	793	
5°	737	65
15°	388	107
25°	129	61
35°	36	24
45°	9	7
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1292205

CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DL1GPH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	792.8
1°	791.2
2°	784.7
3°	773.3
4°	757.5
5°	736.8
6°	712.5
7°	685.0
8°	653.2
9°	620.5
10°	583.5
11°	547.0
12°	506.8
13°	467.2
14°	426.6
15°	388.5
17.5°	301.2
20°	228.7
22.5°	171.7
25°	129.0
27.5°	95.6
30°	70.2
32.5°	50.8
35°	36.5
37.5°	25.9
40°	18.1
42.5°	12.4
45°	8.8
47.5°	6.2
50°	4.7
52.5°	3.6
55°	3.1
57.5°	2.8
60°	2.3
62.5°	2.1
65°	2.1
67.5°	1.8
70°	1.6
72.5°	1.3
75°	1.0
77.5°	0.8
80°	0.5
82.5°	0.5
85°	0.3
87.5°	0.3



TEST NUMBER: P1292205  
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DL1GPH\_2700K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)