

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290124

Luminaire Tested: P3AS05R50W2N902765DE010 E3CD1MB_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290124
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R50W2N902765DE010 E3CD1MB_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI ,
E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 491.1 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290124

CATALOG NUMBER: P3AS05R50W2N902765DE010 E3CD1MB_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1290124

CATALOG NUMBER: P3AS05R50W2N902765DE010 E3CD1MB_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	114	112	109	107		112	109	107	106		105	104	102		102	101	99		98	97	96		95			
2	109	105	101	98		107	103	100	97		100	97	95		97	95	93		94	93	91		90			
3	105	99	95	91		103	98	94	90		95	92	89		93	90	88		91	88	86		85			
4	100	94	89	85		99	92	88	85		90	87	84		88	85	83		87	84	82		80			
5	96	89	84	80		94	88	83	79		86	82	79		84	81	78		83	80	77		76			
6	92	84	79	75		91	83	79	75		82	78	74		81	77	74		79	76	73		72			
7	88	80	75	71		87	79	74	71		78	74	71		77	73	70		76	73	70		69			
8	85	76	71	67		83	76	71	67		75	70	67		74	70	67		73	69	66		65			
9	81	73	68	64		80	72	67	64		71	67	64		71	66	63		70	66	63		62			
10	78	69	64	61		77	69	64	61		68	64	61		68	63	61		67	63	60		59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	170995
5°	167950
10°	161253
15°	147856
20°	130398
25°	99949
30°	54337
35°	17480
40°	4122
45°	558
50°	478
55°	535
60°	482
65°	571
70°	449
75°	593
80°	505
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 85°

Luminance: 1006 cd/sqm

TEST NUMBER: P1290124

CATALOG NUMBER: P3AS05R50W2N902765DE010 E3CD1MB_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.6	14.6
10°-20°	181.1	36.9
20°-30°	181.3	36.9
30°-40°	51.0	10.4
40°-50°	3.1	0.6
50°-60°	1.2	0.2
60°-70°	0.9	0.2
70°-80°	0.6	0.1
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	434.0	88.4
0°-40°	485.0	98.8
0°-60°	489.2	99.6
0°-90°	491.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	491.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	780	
5°	763	72
15°	651	181
25°	413	181
35°	65	51
45°	2	3
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1290124

CATALOG NUMBER: P3AS05R50W2N902765DE010 E3CD1MB_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	779.8
2.5°	775.9
5°	763.0
7.5°	745.4
10°	724.2
12.5°	692.3
15°	651.3
17.5°	604.3
20°	558.8
22.5°	502.1
25°	413.1
27.5°	307.6
30°	214.6
32.5°	129.6
35°	65.3
37.5°	30.9
40°	14.4
42.5°	5.4
45°	1.8
47.5°	1.4
50°	1.4
52.5°	1.4
55°	1.4
57.5°	1.1
60°	1.1
62.5°	1.1
65°	1.1
67.5°	0.7
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)