

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292254

Luminaire Tested: P3AS09R25W2N902750DE010 E3DLD1MW\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292254  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R25W2N902750DE010 E3DLD1MW\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,  
E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 472.0 lumens  
Efficiency: N/A  
Efficacy: 52.4 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292254  
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DLD1MW\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1292254  
 CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DLD1MW\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93		91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85		83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78		76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71		70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66		64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61		59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57		55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53		51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49		48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46		45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	112184
5°	109509
10°	101468
15°	90375
20°	77660
25°	66004
30°	54337
35°	42349
40°	30457
45°	19320
50°	11428
55°	7875
60°	7236
65°	6693
70°	6027
75°	5507
80°	5177
85°	4529

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19320 cd/sqm



TEST NUMBER: P1292254

CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DLD1MW\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.1	9.8
10°-20°	110.5	23.4
20°-30°	124.9	26.5
30°-40°	98.8	20.9
40°-50°	49.9	10.6
50°-60°	20.0	4.2
60°-70°	12.8	2.7
70°-80°	7.1	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	281.5	59.6
0°-40°	380.3	80.6
0°-60°	450.1	95.4
0°-90°	472.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	472.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	512	
5°	498	46
15°	398	111
25°	273	125
35°	158	99
45°	62	50
55°	21	20
65°	13	13
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1292254  
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DLD1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	511.6
1°	511.6
2°	509.8
3°	506.9
4°	502.8
5°	497.5
6°	491.0
7°	483.3
8°	475.1
9°	465.7
10°	455.7
11°	444.5
12°	434.0
13°	421.6
14°	409.8
15°	398.1
17.5°	365.2
20°	332.8
22.5°	302.2
25°	272.8
27.5°	244.0
30°	214.6
32.5°	187.0
35°	158.2
37.5°	131.7
40°	106.4
42.5°	82.9
45°	62.3
47.5°	46.5
50°	33.5
52.5°	25.3
55°	20.6
57.5°	18.8
60°	16.5
62.5°	14.7
65°	12.9
67.5°	11.2
70°	9.4
72.5°	8.2
75°	6.5
77.5°	5.3
80°	4.1
82.5°	2.9
85°	1.8
87.5°	0.6



TEST NUMBER: P1292254  
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3DLD1MW\_5000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)