

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292304

Luminaire Tested: P3AS09R25W2N902750DE010 E3PHLD1MW_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292304
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25W2N902750DE010 E3PHLD1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 472.0 lumens
Efficiency: N/A
Efficacy: 52.4 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.71
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292304
CATALOG NUMBER: P3AS09R25W2N902750DE010 E3PHLD1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1292304

CATALOG NUMBER: P3AS09R25W2N902750DE010 E3PHLD1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	83	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59
6	81	70	63	58	79	69	62	57	68	62	57	66	61	57	65	60	56	55
7	76	65	58	53	75	64	58	53	63	57	53	62	56	52	61	56	52	50
8	72	61	54	49	71	60	54	49	59	53	49	58	53	49	57	52	48	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	43	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123148
5°	116905
10°	101245
15°	82430
20°	65129
25°	51922
30°	42108
35°	34291
40°	28425
45°	23940
50°	20264
55°	17854
60°	15613
65°	13646
70°	11989
75°	10082
80°	7450
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 23940 cd/sqm



TEST NUMBER: P1292304

CATALOG NUMBER: P3AS09R25W2N902750DE010 E3PHLD1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.2	10.2
10°-20°	100.7	21.3
20°-30°	99.2	21.0
30°-40°	80.8	17.1
40°-50°	60.0	12.7
50°-60°	41.9	8.9
60°-70°	26.2	5.6
70°-80°	12.6	2.7
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	248.1	52.6
0°-40°	328.9	69.7
0°-60°	430.7	91.3
0°-90°	472.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	472.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	562	
5°	531	48
15°	363	101
25°	215	99
35°	128	81
45°	77	60
55°	47	42
65°	26	26
75°	12	13
85°	2	2
90°	0	



TEST NUMBER: P1292304

CATALOG NUMBER: P3AS09R25W2N902750DE010 E3PHLD1MW_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	561.6
2.5°	554.0
5°	531.1
7.5°	496.3
10°	454.7
12.5°	408.9
15°	363.1
17.5°	318.1
20°	279.1
22.5°	245.2
25°	214.6
27.5°	188.3
30°	166.3
32.5°	145.9
35°	128.1
37.5°	112.8
40°	99.3
42.5°	87.4
45°	77.2
47.5°	67.9
50°	59.4
52.5°	52.6
55°	46.7
57.5°	40.7
60°	35.6
62.5°	30.5
65°	26.3
67.5°	22.1
70°	18.7
72.5°	15.3
75°	11.9
77.5°	8.5
80°	5.9
82.5°	3.4
85°	1.7
87.5°	0.8
90°	0.0

(END OF REPORT)