

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292313

Luminaire Tested: P3AS09R25W2N902765DE010 E3CB1MB\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292313  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R25W2N902765DE010 E3CB1MB\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,  
E3CB1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 753.1 lumens  
Efficiency: N/A  
Efficacy: 83.7 lumens/watt  
Spacing Criteria (0/90/45): 0.45 / 0.45 / 0.41  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292313  
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3CB1MB\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1292313

CATALOG NUMBER: P3AS09R25W2N902765DE010 E3CB1MB\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 99 | 99 | 100 |
| 1   | 115 | 113 | 111 | 110 | 113 | 111 | 109 | 108 | 107 | 106 | 105 | 103 | 103 | 102 | 100 | 99  | 99  | 97  | 97 | 97 | 97  |
| 2   | 112 | 108 | 105 | 103 | 110 | 107 | 104 | 102 | 104 | 102 | 100 | 101 | 99  | 98  | 98  | 97  | 96  | 94  | 94 | 94 | 94  |
| 3   | 108 | 104 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 98  | 96  | 98  | 96  | 94  | 96  | 94  | 93  | 92  | 92 | 92 | 92  |
| 4   | 105 | 100 | 97  | 94  | 104 | 99  | 96  | 93  | 97  | 95  | 92  | 96  | 93  | 91  | 94  | 92  | 90  | 89  | 89 | 89 | 89  |
| 5   | 103 | 97  | 93  | 90  | 101 | 96  | 93  | 90  | 95  | 92  | 89  | 93  | 91  | 89  | 92  | 90  | 88  | 87  | 87 | 87 | 87  |
| 6   | 100 | 94  | 90  | 87  | 99  | 93  | 90  | 87  | 92  | 89  | 87  | 91  | 88  | 86  | 90  | 87  | 86  | 85  | 85 | 85 | 85  |
| 7   | 97  | 91  | 88  | 85  | 96  | 91  | 87  | 85  | 90  | 87  | 84  | 89  | 86  | 84  | 88  | 85  | 83  | 83  | 83 | 83 | 83  |
| 8   | 95  | 89  | 85  | 83  | 94  | 89  | 85  | 82  | 88  | 84  | 82  | 87  | 84  | 82  | 86  | 83  | 81  | 81  | 81 | 81 | 81  |
| 9   | 93  | 87  | 83  | 80  | 92  | 86  | 83  | 80  | 86  | 82  | 80  | 85  | 82  | 80  | 84  | 82  | 80  | 79  | 79 | 79 | 79  |
| 10  | 91  | 85  | 81  | 78  | 90  | 84  | 81  | 78  | 84  | 80  | 78  | 83  | 80  | 78  | 82  | 80  | 78  | 77  | 77 | 77 | 77  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 805067 |
| 5°  | 746685 |
| 10° | 579059 |
| 15° | 290354 |
| 20° | 95395  |
| 25° | 37938  |
| 30° | 14230  |
| 35° | 4122   |
| 40° | 1861   |
| 45° | 744    |
| 50° | 614    |
| 55° | 459    |
| 60° | 526    |
| 65° | 623    |
| 70° | 385    |
| 75° | 508    |
| 80° | 758    |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 80°  
 Luminance: 758 cd/sqm



TEST NUMBER: P1292313

CATALOG NUMBER: P3AS09R25W2N902765DE010 E3CB1MB\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 298.4  | 39.6      |
| 10°-20°   | 356.0  | 47.3      |
| 20°-30°   | 80.2   | 10.7      |
| 30°-40°   | 13.0   | 1.7       |
| 40°-50°   | 2.4    | 0.3       |
| 50°-60°   | 1.3    | 0.2       |
| 60°-70°   | 1.1    | 0.1       |
| 70°-80°   | 0.6    | 0.1       |
| 80°-90°   | 0.1    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 734.6  | 97.5      |
| 0°-40°    | 747.6  | 99.3      |
| 0°-60°    | 751.2  | 99.8      |
| 0°-90°    | 753.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 753.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3671 |      |
| 5°  | 3392 | 298  |
| 15° | 1279 | 356  |
| 25° | 157  | 80   |
| 35° | 15   | 13   |
| 45° | 2    | 2    |
| 55° | 1    | 1    |
| 65° | 1    | 1    |
| 75° | 1    | 1    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P1292313

CATALOG NUMBER: P3AS09R25W2N902765DE010 E3CB1MB\_4000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3671.4 |
| 1°    | 3665.5 |
| 2°    | 3635.9 |
| 3°    | 3581.5 |
| 4°    | 3499.2 |
| 5°    | 3392.2 |
| 6°    | 3264.4 |
| 7°    | 3126.0 |
| 8°    | 2967.4 |
| 9°    | 2794.1 |
| 10°   | 2600.6 |
| 11°   | 2377.6 |
| 12°   | 2120.8 |
| 13°   | 1852.3 |
| 14°   | 1564.2 |
| 15°   | 1279.0 |
| 17.5° | 728.8  |
| 20°   | 408.8  |
| 22.5° | 246.7  |
| 25°   | 156.8  |
| 27.5° | 96.4   |
| 30°   | 56.2   |
| 32.5° | 29.6   |
| 35°   | 15.4   |
| 37.5° | 10.1   |
| 40°   | 6.5    |
| 42.5° | 4.1    |
| 45°   | 2.4    |
| 47.5° | 1.8    |
| 50°   | 1.8    |
| 52.5° | 1.8    |
| 55°   | 1.2    |
| 57.5° | 1.2    |
| 60°   | 1.2    |
| 62.5° | 1.2    |
| 65°   | 1.2    |
| 67.5° | 1.2    |
| 70°   | 0.6    |
| 72.5° | 0.6    |
| 75°   | 0.6    |
| 77.5° | 0.6    |
| 80°   | 0.6    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |



TEST NUMBER: P1292313

CATALOG NUMBER: P3AS09R25W2N902765DE010 E3CB1MB\_4000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)