

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290239

Luminaire Tested: P3AS05R50W2N902765DE010 E3DLD1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290239
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R50W2N902765DE010 E3DLD1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 346.0 lumens
Efficiency: N/A
Efficacy: 58.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290239

CATALOG NUMBER: P3AS05R50W2N902765DE010 E3DLD1WMH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1290239

CATALOG NUMBER: P3AS05R50W2N902765DE010 E3DLD1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70323
5°	69271
10°	66220
15°	61317
20°	55095
25°	48438
30°	41196
35°	33408
40°	25104
45°	16157
50°	7676
55°	6040
60°	5701
65°	5344
70°	4809
75°	4321
80°	4041
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16157 cd/sqm

TEST NUMBER: P1290239

CATALOG NUMBER: P3AS05R50W2N902765DE010 E3DLD1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.5	8.5
10°-20°	75.3	21.8
20°-30°	91.5	26.4
30°-40°	77.6	22.4
40°-50°	40.3	11.7
50°-60°	14.5	4.2
60°-70°	10.1	2.9
70°-80°	5.4	1.6
80°-90°	1.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	196.3	56.7
0°-40°	273.9	79.2
0°-60°	328.8	95.0
0°-90°	346.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	346.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	321	
5°	315	30
15°	270	75
25°	200	92
35°	125	78
45°	52	40
55°	16	15
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1290239

CATALOG NUMBER: P3AS05R50W2N902765DE010 E3DLD1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	320.7
2.5°	319.5
5°	314.7
7.5°	307.6
10°	297.4
12.5°	284.3
15°	270.1
17.5°	253.9
20°	236.1
22.5°	218.0
25°	200.2
27.5°	181.7
30°	162.7
32.5°	143.7
35°	124.8
37.5°	106.2
40°	87.7
42.5°	69.9
45°	52.1
47.5°	34.8
50°	22.5
52.5°	17.4
55°	15.8
57.5°	14.2
60°	13.0
62.5°	11.5
65°	10.3
67.5°	8.7
70°	7.5
72.5°	6.3
75°	5.1
77.5°	3.9
80°	3.2
82.5°	2.4
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)