

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290252

Luminaire Tested: P3AS05R50W2N902765DE010 E3DLP1H\_3500K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1290252  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R50W2N902765DE010 E3DLP1H\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3500K CCT AND, 90CRI ,  
E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 296.0 lumens  
Efficiency: N/A  
Efficacy: 50.2 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1290252

CATALOG NUMBER: P3AS05R50W2N902765DE010 E3DLP1H\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1290252

CATALOG NUMBER: P3AS05R50W2N902765DE010 E3DLP1H\_3500K

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|--|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |  |  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |  |  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |  |  |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |  |  |
| 1   | 113 | 110 | 107 | 105 | 111 | 108 | 106 | 103 | 104 | 102 | 100 | 100 | 99  | 97  | 97  | 95  | 94  | 93  |  |  |
| 2   | 107 | 102 | 98  | 94  | 105 | 100 | 96  | 93  | 97  | 94  | 91  | 94  | 91  | 89  | 91  | 89  | 87  | 85  |  |  |
| 3   | 101 | 95  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 83  | 88  | 85  | 82  | 86  | 83  | 81  | 79  |  |  |
| 4   | 96  | 88  | 82  | 78  | 94  | 87  | 82  | 78  | 85  | 80  | 77  | 83  | 79  | 76  | 81  | 78  | 75  | 73  |  |  |
| 5   | 91  | 83  | 76  | 72  | 90  | 82  | 76  | 72  | 80  | 75  | 71  | 78  | 74  | 70  | 77  | 73  | 70  | 68  |  |  |
| 6   | 87  | 77  | 71  | 67  | 85  | 77  | 71  | 67  | 75  | 70  | 66  | 74  | 69  | 66  | 72  | 68  | 65  | 64  |  |  |
| 7   | 82  | 73  | 67  | 62  | 81  | 72  | 66  | 62  | 71  | 66  | 62  | 70  | 65  | 61  | 68  | 64  | 61  | 60  |  |  |
| 8   | 78  | 69  | 63  | 58  | 77  | 68  | 62  | 58  | 67  | 62  | 58  | 66  | 61  | 58  | 65  | 61  | 57  | 56  |  |  |
| 9   | 75  | 65  | 59  | 55  | 74  | 64  | 59  | 55  | 63  | 58  | 55  | 63  | 58  | 54  | 62  | 57  | 54  | 53  |  |  |
| 10  | 71  | 61  | 56  | 52  | 70  | 61  | 55  | 52  | 60  | 55  | 51  | 59  | 55  | 51  | 59  | 54  | 51  | 50  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°    |
|-----|-------|
| 0°  | 86090 |
| 5°  | 83777 |
| 10° | 77242 |
| 15° | 67946 |
| 20° | 56845 |
| 25° | 45075 |
| 30° | 33068 |
| 35° | 22727 |
| 40° | 14456 |
| 45° | 8063  |
| 50° | 4367  |
| 55° | 3670  |
| 60° | 3158  |
| 65° | 2906  |
| 70° | 2565  |
| 75° | 2372  |
| 80° | 2020  |
| 85° | 2013  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle:  $0^\circ$ 

Vertical Angle:  $45^\circ$

Luminance: 8063 cd/sqm

TEST NUMBER: P1290252

CATALOG NUMBER: P3AS05R50W2N902765DE010 E3DLP1H\_3500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 35.3   | 11.9      |
| 10°-20°   | 82.9   | 28.0      |
| 20°-30°   | 84.8   | 28.6      |
| 30°-40°   | 53.8   | 18.2      |
| 40°-50°   | 21.4   | 7.2       |
| 50°-60°   | 8.7    | 2.9       |
| 60°-70°   | 5.5    | 1.9       |
| 70°-80°   | 2.8    | 1.0       |
| 80°-90°   | 0.9    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 202.9  | 68.6      |
| 0°-40°    | 256.7  | 86.7      |
| 0°-60°    | 286.7  | 96.9      |
| 0°-90°    | 296.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 296.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 393 |      |
| 5°  | 381 | 35   |
| 15° | 299 | 83   |
| 25° | 186 | 85   |
| 35° | 85  | 54   |
| 45° | 26  | 21   |
| 55° | 10  | 9    |
| 65° | 6   | 6    |
| 75° | 3   | 3    |
| 85° | 1   | 1    |
| 90° | 0   |      |

TEST NUMBER: P1290252

CATALOG NUMBER: P3AS05R50W2N902765DE010 E3DLP1H\_3500K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 392.6 |
| 2.5°  | 389.8 |
| 5°    | 380.6 |
| 7.5°  | 366.2 |
| 10°   | 346.9 |
| 12.5° | 324.1 |
| 15°   | 299.3 |
| 17.5° | 272.0 |
| 20°   | 243.6 |
| 22.5° | 215.1 |
| 25°   | 186.3 |
| 27.5° | 157.4 |
| 30°   | 130.6 |
| 32.5° | 106.6 |
| 35°   | 84.9  |
| 37.5° | 66.5  |
| 40°   | 50.5  |
| 42.5° | 37.3  |
| 45°   | 26.0  |
| 47.5° | 17.6  |
| 50°   | 12.8  |
| 52.5° | 10.8  |
| 55°   | 9.6   |
| 57.5° | 8.4   |
| 60°   | 7.2   |
| 62.5° | 6.4   |
| 65°   | 5.6   |
| 67.5° | 4.8   |
| 70°   | 4.0   |
| 72.5° | 3.2   |
| 75°   | 2.8   |
| 77.5° | 2.0   |
| 80°   | 1.6   |
| 82.5° | 1.2   |
| 85°   | 0.8   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)