

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292400

Luminaire Tested: P3AS09R25W2N902765DE010 E3DL1WH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292400
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25W2N902765DE010 E3DL1WH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,
E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 339.0 lumens
Efficiency: N/A
Efficacy: 37.7 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292400
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DL1WH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1292400

CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DL1WH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	123082
5°	118071
10°	103449
15°	83156
20°	63892
25°	48342
30°	34917
35°	23209
40°	14084
45°	8187
50°	5219
55°	4244
60°	3728
65°	3269
70°	2693
75°	2711
80°	2020
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8187 cd/sqm



TEST NUMBER: P1292400

CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DL1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.8	14.4
10°-20°	101.3	29.9
20°-30°	91.6	27.0
30°-40°	55.0	16.2
40°-50°	21.8	6.4
50°-60°	10.1	3.0
60°-70°	6.1	1.8
70°-80°	3.3	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	241.7	71.3
0°-40°	296.7	87.5
0°-60°	328.7	96.9
0°-90°	339.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	339.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	561	
5°	536	49
15°	366	101
25°	200	92
35°	87	55
45°	26	22
55°	11	10
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1292400

CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DL1WH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	561.3
1°	561.3
2°	558.6
3°	552.8
4°	545.4
5°	536.4
6°	524.8
7°	511.6
8°	496.3
9°	480.9
10°	464.6
11°	445.5
12°	426.0
13°	406.4
14°	386.9
15°	366.3
17.5°	317.6
20°	273.8
22.5°	234.1
25°	199.8
27.5°	167.5
30°	137.9
32.5°	111.0
35°	86.7
37.5°	66.1
40°	49.2
42.5°	35.9
45°	26.4
47.5°	20.1
50°	15.3
52.5°	12.7
55°	11.1
57.5°	9.5
60°	8.5
62.5°	6.9
65°	6.3
67.5°	5.3
70°	4.2
72.5°	3.7
75°	3.2
77.5°	2.6
80°	1.6
82.5°	1.1
85°	1.1
87.5°	0.5



TEST NUMBER: P1292400
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DL1WH_2700K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)