

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292405

Luminaire Tested: P3AS09R25W2N902765DE010 E3DL1WH\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292405  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R25W2N902765DE010 E3DL1WH\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 6500K CCT AND, 90CRI ,  
E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 377.0 lumens  
Efficiency: N/A  
Efficacy: 41.9 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292405  
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DL1WH\_6500K

### Luminous Intensity Polar Plot







TEST NUMBER: P1292405

CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DL1WH\_6500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 54.3   | 14.4      |
| 10°-20°   | 112.6  | 29.9      |
| 20°-30°   | 101.9  | 27.0      |
| 30°-40°   | 61.2   | 16.2      |
| 40°-50°   | 24.3   | 6.4       |
| 50°-60°   | 11.2   | 3.0       |
| 60°-70°   | 6.8    | 1.8       |
| 70°-80°   | 3.6    | 1.0       |
| 80°-90°   | 1.1    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 268.8  | 71.3      |
| 0°-40°    | 330.0  | 87.5      |
| 0°-60°    | 365.5  | 96.9      |
| 0°-90°    | 377.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 377.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 624 |      |
| 5°  | 597 | 54   |
| 15° | 407 | 113  |
| 25° | 222 | 102  |
| 35° | 96  | 61   |
| 45° | 29  | 24   |
| 55° | 12  | 11   |
| 65° | 7   | 7    |
| 75° | 4   | 4    |
| 85° | 1   | 1    |
| 90° | 0   |      |



TEST NUMBER: P1292405  
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DL1WH\_6500K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 624.2 |
| 1°    | 624.2 |
| 2°    | 621.2 |
| 3°    | 614.8 |
| 4°    | 606.6 |
| 5°    | 596.6 |
| 6°    | 583.6 |
| 7°    | 568.9 |
| 8°    | 551.9 |
| 9°    | 534.8 |
| 10°   | 516.6 |
| 11°   | 495.5 |
| 12°   | 473.7 |
| 13°   | 452.0 |
| 14°   | 430.2 |
| 15°   | 407.3 |
| 17.5° | 353.2 |
| 20°   | 304.5 |
| 22.5° | 260.4 |
| 25°   | 222.2 |
| 27.5° | 186.3 |
| 30°   | 153.4 |
| 32.5° | 123.4 |
| 35°   | 96.4  |
| 37.5° | 73.5  |
| 40°   | 54.7  |
| 42.5° | 40.0  |
| 45°   | 29.4  |
| 47.5° | 22.3  |
| 50°   | 17.0  |
| 52.5° | 14.1  |
| 55°   | 12.3  |
| 57.5° | 10.6  |
| 60°   | 9.4   |
| 62.5° | 7.6   |
| 65°   | 7.1   |
| 67.5° | 5.9   |
| 70°   | 4.7   |
| 72.5° | 4.1   |
| 75°   | 3.5   |
| 77.5° | 2.9   |
| 80°   | 1.8   |
| 82.5° | 1.2   |
| 85°   | 1.2   |
| 87.5° | 0.6   |



TEST NUMBER: P1292405

CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DL1WH\_6500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)