

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292415

Luminaire Tested: P3AS09R25W2N902765DE010 E3DLD1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292415
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25W2N902765DE010 E3DLD1GPH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 233.0 lumens
Efficiency: N/A
Efficacy: 25.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292415
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLD1GPH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1292415

CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLD1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.8	9.8
10°-20°	54.6	23.4
20°-30°	61.6	26.5
30°-40°	48.7	20.9
40°-50°	24.6	10.6
50°-60°	9.9	4.2
60°-70°	6.3	2.7
70°-80°	3.5	1.5
80°-90°	1.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	139.0	59.6
0°-40°	187.7	80.6
0°-60°	222.2	95.4
0°-90°	233.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	233.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	252	
5°	246	23
15°	196	55
25°	135	62
35°	78	49
45°	31	25
55°	10	10
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1292415
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLD1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	252.5
1°	252.5
2°	251.7
3°	250.2
4°	248.2
5°	245.6
6°	242.4
7°	238.6
8°	234.5
9°	229.9
10°	225.0
11°	219.4
12°	214.2
13°	208.1
14°	202.3
15°	196.5
17.5°	180.3
20°	164.3
22.5°	149.2
25°	134.7
27.5°	120.5
30°	105.9
32.5°	92.3
35°	78.1
37.5°	65.0
40°	52.5
42.5°	40.9
45°	30.8
47.5°	22.9
50°	16.5
52.5°	12.5
55°	10.2
57.5°	9.3
60°	8.1
62.5°	7.3
65°	6.4
67.5°	5.5
70°	4.6
72.5°	4.1
75°	3.2
77.5°	2.6
80°	2.0
82.5°	1.5
85°	0.9
87.5°	0.3



TEST NUMBER: P1292415
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLD1GPH_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)