

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290410

Luminaire Tested: P3AS05R55W2N902750DE010 E3DLP1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290410
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R55W2N902750DE010 E3DLP1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI ,
E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 261.0 lumens
Efficiency: N/A
Efficacy: 44.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290410

CATALOG NUMBER: P3AS05R55W2N902750DE010 E3DLP1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1290410

CATALOG NUMBER: P3AS05R55W2N902750DE010 E3DLP1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		97	95	94
2	107	102	97	94		105	100	96	93		97	93	91		94	91	89		91	89	87
3	101	94	89	85		99	93	88	84		90	86	83		88	84	81		85	83	80
4	96	88	82	77		94	87	81	77		84	80	76		82	78	75		80	77	74
5	91	82	76	71		89	81	75	71		79	74	70		77	73	70		76	72	69
6	86	77	70	66		84	76	70	66		74	69	65		73	68	65		72	68	64
7	82	72	66	61		80	71	65	61		70	65	61		69	64	60		68	63	60
8	78	68	62	57		76	67	61	57		66	61	57		65	60	57		64	60	56
9	74	64	58	54		73	63	58	54		62	57	53		62	57	53		61	56	53
10	70	60	55	51		69	60	54	50		59	54	50		58	54	50		58	53	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71003
5°	69227
10°	64350
15°	57299
20°	48701
25°	39293
30°	29954
35°	21308
40°	14055
45°	8342
50°	4878
55°	3020
60°	2675
65°	2439
70°	2052
75°	1864
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8342 cd/sqm

TEST NUMBER: P1290410

CATALOG NUMBER: P3AS05R55W2N902750DE010 E3DLP1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.2	11.2
10°-20°	70.0	26.8
20°-30°	74.1	28.4
30°-40°	50.1	19.2
40°-50°	21.9	8.4
50°-60°	7.9	3.0
60°-70°	4.6	1.8
70°-80°	2.4	0.9
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	173.3	66.4
0°-40°	223.4	85.6
0°-60°	253.2	97.0
0°-90°	261.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	261.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	324	
5°	314	29
15°	252	70
25°	162	74
35°	80	50
45°	27	22
55°	8	8
65°	5	5
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1290410

CATALOG NUMBER: P3AS05R55W2N902750DE010 E3DLP1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	323.8
2.5°	321.3
5°	314.5
7.5°	303.3
10°	289.0
12.5°	271.8
15°	252.4
17.5°	230.9
20°	208.7
22.5°	185.4
25°	162.4
27.5°	139.8
30°	118.3
32.5°	97.9
35°	79.6
37.5°	63.1
40°	49.1
42.5°	36.9
45°	26.9
47.5°	19.7
50°	14.3
52.5°	10.0
55°	7.9
57.5°	7.2
60°	6.1
62.5°	5.4
65°	4.7
67.5°	3.9
70°	3.2
72.5°	2.9
75°	2.2
77.5°	1.8
80°	1.4
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)