

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290447

Luminaire Tested: P3AS05R55W2N902765DE010 E3CD1MB_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290447
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R55W2N902765DE010 E3CD1MB_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 90CRI ,
E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 531.0 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290447

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3CD1MB_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1290447

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3CD1MB_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89			
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84			
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	85	83	80	79			
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76	74			
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70			
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66			
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63			
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61	60			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147269
5°	145916
10°	151767
15°	149672
20°	138005
25°	112289
30°	68213
35°	23610
40°	6727
45°	3225
50°	1365
55°	612
60°	702
65°	623
70°	513
75°	678
80°	505
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3225 cd/sqm

TEST NUMBER: P1290447

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3CD1MB_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.1	12.1
10°-20°	183.2	34.5
20°-30°	204.3	38.5
30°-40°	66.8	12.6
40°-50°	8.8	1.7
50°-60°	1.9	0.4
60°-70°	1.1	0.2
70°-80°	0.7	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	451.6	85.0
0°-40°	518.4	97.6
0°-60°	529.1	99.6
0°-90°	531.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	531.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	672	
5°	663	64
15°	659	183
25°	464	204
35°	88	67
45°	10	9
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1290447

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3CD1MB_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	671.6
2.5°	666.8
5°	662.9
7.5°	672.4
10°	681.6
12.5°	676.8
15°	659.3
17.5°	631.3
20°	591.4
22.5°	536.3
25°	464.1
27.5°	372.3
30°	269.4
32.5°	165.2
35°	88.2
37.5°	44.7
40°	23.5
42.5°	15.2
45°	10.4
47.5°	7.2
50°	4.0
52.5°	2.4
55°	1.6
57.5°	1.6
60°	1.6
62.5°	1.2
65°	1.2
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)