

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292440

Luminaire Tested: P3AS09R25W2N902765DE010 E3DLD1WH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292440  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R25W2N902765DE010 E3DLD1WH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 472.0 lumens  
Efficiency: N/A  
Efficacy: 52.4 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292440  
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLD1WH\_5000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1292440  
 CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLD1WH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.1	9.8
10°-20°	110.5	23.4
20°-30°	124.9	26.5
30°-40°	98.8	20.9
40°-50°	49.9	10.6
50°-60°	20.0	4.2
60°-70°	12.8	2.7
70°-80°	7.1	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	281.5	59.6
0°-40°	380.3	80.6
0°-60°	450.1	95.4
0°-90°	472.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	472.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	512	
5°	498	46
15°	398	111
25°	273	125
35°	158	99
45°	62	50
55°	21	20
65°	13	13
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1292440  
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLD1WH\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	511.6
1°	511.6
2°	509.8
3°	506.9
4°	502.8
5°	497.5
6°	491.0
7°	483.3
8°	475.1
9°	465.7
10°	455.7
11°	444.5
12°	434.0
13°	421.6
14°	409.8
15°	398.1
17.5°	365.2
20°	332.8
22.5°	302.2
25°	272.8
27.5°	244.0
30°	214.6
32.5°	187.0
35°	158.2
37.5°	131.7
40°	106.4
42.5°	82.9
45°	62.3
47.5°	46.5
50°	33.5
52.5°	25.3
55°	20.6
57.5°	18.8
60°	16.5
62.5°	14.7
65°	12.9
67.5°	11.2
70°	9.4
72.5°	8.2
75°	6.5
77.5°	5.3
80°	4.1
82.5°	2.9
85°	1.8
87.5°	0.6



TEST NUMBER: P1292440  
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLD1WH\_5000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)