

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290528

Luminaire Tested: P3AS05R55W2N902765DE010 E3DLD1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290528
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R55W2N902765DE010 E3DLD1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 164.0 lumens
Efficiency: N/A
Efficacy: 27.8 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290528
CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLD1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1290528

CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLD1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.0	7.9
10°-20°	33.7	20.5
20°-30°	42.2	25.7
30°-40°	37.6	23.0
40°-50°	22.0	13.4
50°-60°	7.6	4.7
60°-70°	4.6	2.8
70°-80°	2.5	1.5
80°-90°	0.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	88.8	54.2
0°-40°	126.5	77.1
0°-60°	156.1	95.2
0°-90°	164.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	164.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	141	
5°	138	13
15°	120	34
25°	92	42
35°	60	38
45°	28	22
55°	7	8
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1290528
CATALOG NUMBER: P3AS05R55W2N902765DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	140.6
2.5°	139.8
5°	138.3
7.5°	135.2
10°	131.3
12.5°	126.5
15°	120.5
17.5°	114.1
20°	106.9
22.5°	99.6
25°	92.0
27.5°	84.5
30°	76.9
32.5°	68.8
35°	60.4
37.5°	52.3
40°	44.6
42.5°	36.2
45°	27.9
47.5°	21.3
50°	15.5
52.5°	10.1
55°	7.2
57.5°	6.4
60°	5.8
62.5°	5.2
65°	4.6
67.5°	4.1
70°	3.5
72.5°	2.9
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.0
85°	0.6
87.5°	0.4
90°	0.0

(END OF REPORT)