

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292448

Luminaire Tested: P3AS09R25W2N902765DE010 E3DLP1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292448
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R25W2N902765DE010 E3DLP1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 166.0 lumens
Efficiency: N/A
Efficacy: 18.4 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292448
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLP1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1292448

CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLP1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60258
5°	57825
10°	50656
15°	40704
20°	31293
25°	23663
30°	17091
35°	11350
40°	6899
45°	4000
50°	2559
55°	2064
60°	1798
65°	1608
70°	1346
75°	1356
80°	1010
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4000 cd/sqm



TEST NUMBER: P1292448

CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLP1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.9	14.4
10°-20°	49.6	29.9
20°-30°	44.8	27.0
30°-40°	26.9	16.2
40°-50°	10.7	6.4
50°-60°	4.9	3.0
60°-70°	3.0	1.8
70°-80°	1.6	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	118.3	71.3
0°-40°	145.3	87.5
0°-60°	160.9	96.9
0°-90°	166.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	166.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	275	
5°	263	24
15°	179	50
25°	98	45
35°	42	27
45°	13	11
55°	5	5
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1292448
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	274.8
1°	274.8
2°	273.5
3°	270.7
4°	267.1
5°	262.7
6°	257.0
7°	250.5
8°	243.0
9°	235.5
10°	227.5
11°	218.2
12°	208.6
13°	199.0
14°	189.4
15°	179.3
17.5°	155.5
20°	134.1
22.5°	114.6
25°	97.8
27.5°	82.0
30°	67.5
32.5°	54.3
35°	42.4
37.5°	32.3
40°	24.1
42.5°	17.6
45°	12.9
47.5°	9.8
50°	7.5
52.5°	6.2
55°	5.4
57.5°	4.7
60°	4.1
62.5°	3.4
65°	3.1
67.5°	2.6
70°	2.1
72.5°	1.8
75°	1.6
77.5°	1.3
80°	0.8
82.5°	0.5
85°	0.5
87.5°	0.3



TEST NUMBER: P1292448
CATALOG NUMBER: P3AS09R25W2N902765DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)