

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290648

Luminaire Tested: P3AS05R60W2N902750DE010 E3D1WH_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290648
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R60W2N902750DE010 E3D1WH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 90CRI ,
E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 478.0 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290648
CATALOG NUMBER: P3AS05R60W2N902750DE010 E3D1WH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1290648

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3D1WH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94				94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88				88
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82				82
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77				77
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	71	69	67				67
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63				63
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59				59
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56				56
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53				53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125253
5°	118226
10°	115162
15°	112532
20°	104636
25°	93538
30°	71454
35°	41251
40°	16001
45°	6667
50°	1467
55°	229
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6667 cd/sqm



TEST NUMBER: P1290648

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3D1WH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.7	10.6
10°-20°	138.1	28.9
20°-30°	172.9	36.2
30°-40°	96.7	20.2
40°-50°	18.4	3.8
50°-60°	1.0	0.2
60°-70°	0.2	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	361.7	75.7
0°-40°	458.4	95.9
0°-60°	477.7	99.9
0°-90°	478.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	478.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	571	
5°	537	51
15°	496	138
25°	387	173
35°	154	97
45°	22	18
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1290648
CATALOG NUMBER: P3AS05R60W2N902750DE010 E3D1WH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	571.2
1°	568.8
2°	561.4
3°	552.6
4°	544.4
5°	537.1
6°	531.7
7°	527.0
8°	523.4
9°	520.1
10°	517.2
11°	514.3
12°	510.9
13°	506.8
14°	501.9
15°	495.7
16°	488.1
17°	479.4
18°	469.7
19°	458.5
20°	448.4
21°	437.4
22°	426.1
23°	414.1
24°	401.0
25°	386.6
26°	369.6
27°	350.6
28°	329.3
29°	306.6
30°	282.2
31°	257.5
32°	232.1
32.5°	218.2
33°	205.7
34°	179.7
35°	154.1
36°	131.0
37°	106.6
37.5°	95.4
38°	84.5
39°	68.0
40°	55.9
42.5°	34.0
45°	21.5



TEST NUMBER: P1290648
CATALOG NUMBER: P3AS05R60W2N902750DE010 E3D1WH_5000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	11.9
50°	4.3
52.5°	1.0
55°	0.6
57.5°	0.4
60°	0.4
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)