

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290653

Luminaire Tested: P3AS05R60W2N902750DE010 E3D1WMH_5000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290653
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R60W2N902750DE010 E3D1WMH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 90CRI ,
E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 478.0 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290653

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3D1WMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1290653

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3D1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	106		111	109	107	105		105	103	102		101	100	99		98	97	96
2	108	104	100	96		106	102	98	95		99	96	93		96	93	91		93	91	89
3	103	97	92	88		101	96	91	88		93	89	86		91	87	85		88	86	84
4	98	91	85	81		96	90	85	81		88	83	80		86	82	79		84	81	78
5	93	85	80	75		92	84	79	75		83	78	74		81	77	74		79	76	73
6	89	80	74	70		87	79	74	70		78	73	70		77	72	69		75	71	69
7	85	76	70	66		83	75	69	65		74	69	65		72	68	65		71	67	64
8	81	71	65	61		79	71	65	61		70	65	61		69	64	61		68	64	61
9	77	67	62	58		76	67	61	58		66	61	57		65	61	57		64	60	57
10	73	64	58	54		72	63	58	54		63	58	54		62	57	54		61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125253
5°	118226
10°	115162
15°	112532
20°	104636
25°	93538
30°	71454
35°	41251
40°	16001
45°	6667
50°	1467
55°	229
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6667 cd/sqm

TEST NUMBER: P1290653

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3D1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.7	10.6
10°-20°	138.1	28.9
20°-30°	172.9	36.2
30°-40°	96.7	20.2
40°-50°	18.4	3.8
50°-60°	1.0	0.2
60°-70°	0.2	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	361.7	75.7
0°-40°	458.4	95.9
0°-60°	477.7	99.9
0°-90°	478.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	478.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	571	
5°	537	51
15°	496	138
25°	387	173
35°	154	97
45°	22	18
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1290653

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3D1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	571.2
1°	568.8
2°	561.4
3°	552.6
4°	544.4
5°	537.1
6°	531.7
7°	527.0
8°	523.4
9°	520.1
10°	517.2
11°	514.3
12°	510.9
13°	506.8
14°	501.9
15°	495.7
16°	488.1
17°	479.4
18°	469.7
19°	458.5
20°	448.4
21°	437.4
22°	426.1
23°	414.1
24°	401.0
25°	386.6
26°	369.6
27°	350.6
28°	329.3
29°	306.6
30°	282.2
31°	257.5
32°	232.1
32.5°	218.2
33°	205.7
34°	179.7
35°	154.1
36°	131.0
37°	106.6
37.5°	95.4
38°	84.5
39°	68.0
40°	55.9
42.5°	34.0
45°	21.5



TEST NUMBER: P1290653

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3D1WMH_5000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	11.9
50°	4.3
52.5°	1.0
55°	0.6
57.5°	0.4
60°	0.4
62.5°	0.2
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)