

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292572

Luminaire Tested: P3AS09R30W2N902750DE010 E3DL1MW\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292572  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R30W2N902750DE010 E3DL1MW\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI ,  
E3DL1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 560.0 lumens  
Efficiency: N/A  
Efficacy: 62.2 lumens/watt  
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292572  
CATALOG NUMBER: P3AS09R30W2N902750DE010 E3DL1MW\_2700K

### Luminous Intensity Polar Plot







TEST NUMBER: P1292572

CATALOG NUMBER: P3AS09R30W2N902750DE010 E3DL1MW\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.2	22.7
10°-20°	226.2	40.4
20°-30°	130.7	23.3
30°-40°	49.6	8.9
40°-50°	15.2	2.7
50°-60°	5.1	0.9
60°-70°	3.5	0.6
70°-80°	1.9	0.3
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	484.1	86.4
0°-40°	533.7	95.3
0°-60°	554.1	98.9
0°-90°	560.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	560.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1490	
5°	1413	127
15°	831	226
25°	275	131
35°	75	50
45°	18	15
55°	5	5
65°	4	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1292572  
CATALOG NUMBER: P3AS09R30W2N902750DE010 E3DL1MW\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1490.2
1°	1489.2
2°	1480.2
3°	1463.2
4°	1442.1
5°	1413.0
6°	1376.0
7°	1334.7
8°	1288.7
9°	1233.7
10°	1174.9
11°	1111.5
12°	1044.3
13°	973.9
14°	902.5
15°	831.1
17.5°	655.4
20°	501.5
22.5°	371.9
25°	275.1
27.5°	200.0
30°	146.0
32.5°	105.3
35°	75.1
37.5°	52.4
40°	37.0
42.5°	25.9
45°	18.5
47.5°	12.7
50°	9.0
52.5°	6.3
55°	5.3
57.5°	4.8
60°	4.2
62.5°	3.7
65°	3.7
67.5°	3.2
70°	2.6
72.5°	2.1
75°	1.6
77.5°	1.6
80°	1.1
82.5°	1.1
85°	0.5
87.5°	0.0



TEST NUMBER: P1292572  
CATALOG NUMBER: P3AS09R30W2N902750DE010 E3DL1MW\_2700K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)