

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292588

Luminaire Tested: P3AS09R30W2N902750DE010 E3DLD1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292588
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R30W2N902750DE010 E3DLD1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 233.0 lumens
Efficiency: N/A
Efficacy: 25.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292588
CATALOG NUMBER: P3AS09R30W2N902750DE010 E3DLD1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1292588
 CATALOG NUMBER: P3AS09R30W2N902750DE010 E3DLD1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91	91	91	91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83	83	83	83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76	76	76	76
4	94	86	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70	70	70	70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64	64	64	64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59	59	59	59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55	55	55	55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51	51	51	51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48	48	48	48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45	45	45	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55039
5°	53819
10°	50032
15°	44518
20°	38293
25°	32445
30°	26941
35°	21121
40°	15143
45°	9924
50°	5663
55°	3708
60°	3508
65°	3269
70°	2949
75°	2626
80°	2526
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9924 cd/sqm



TEST NUMBER: P1292588

CATALOG NUMBER: P3AS09R30W2N902750DE010 E3DLD1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.7	9.7
10°-20°	54.5	23.4
20°-30°	61.5	26.4
30°-40°	49.1	21.1
40°-50°	25.2	10.8
50°-60°	9.5	4.1
60°-70°	6.2	2.7
70°-80°	3.3	1.4
80°-90°	1.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	138.7	59.5
0°-40°	187.7	80.6
0°-60°	222.4	95.5
0°-90°	233.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	233.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	251	
5°	244	23
15°	196	55
25°	134	61
35°	79	49
45°	32	25
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1292588
CATALOG NUMBER: P3AS09R30W2N902750DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	251.0
1°	251.0
2°	250.2
3°	248.7
4°	246.7
5°	244.5
6°	241.6
7°	237.9
8°	233.9
9°	229.3
10°	224.7
11°	219.6
12°	214.1
13°	208.4
14°	202.4
15°	196.1
17.5°	180.1
20°	164.1
22.5°	148.7
25°	134.1
27.5°	119.8
30°	106.4
32.5°	92.6
35°	78.9
37.5°	65.5
40°	52.9
42.5°	41.7
45°	32.0
47.5°	23.7
50°	16.6
52.5°	11.7
55°	9.7
57.5°	8.9
60°	8.0
62.5°	7.1
65°	6.3
67.5°	5.4
70°	4.6
72.5°	3.7
75°	3.1
77.5°	2.6
80°	2.0
82.5°	1.4
85°	0.9
87.5°	0.3



TEST NUMBER: P1292588
CATALOG NUMBER: P3AS09R30W2N902750DE010 E3DLD1GPH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)