

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290768

Luminaire Tested: P3AS05R60W2N902765DE010 E3CD1MMS_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290768
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R60W2N902765DE010 E3CD1MMS_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI ,
E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 464.1 lumens
Efficiency: N/A
Efficacy: 78.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290768

CATALOG NUMBER: P3AS05R60W2N902765DE010 E3CD1MMS_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1290768

CATALOG NUMBER: P3AS05R60W2N902765DE010 E3CD1MMS_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94		
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87		
3	103	96	91	88	101	95	90	87	92	89	85	90	87	84	88	85	83	81		
4	98	90	85	80	96	89	84	80	87	83	79	85	81	78	83	80	77	76		
5	93	84	79	74	91	84	78	74	82	77	73	80	76	73	79	75	72	71		
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	68	66		
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62		
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58		
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55		
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110803
5°	106405
10°	109550
15°	110965
20°	97985
25°	82577
30°	66972
35°	43607
40°	20038
45°	7691
50°	2559
55°	688
60°	614
65°	571
70°	449
75°	593
80°	505
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 7691 cd/sqm

TEST NUMBER: P1290768

CATALOG NUMBER: P3AS05R60W2N902765DE010 E3CD1MMS_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	10.0
10°-20°	133.9	28.8
20°-30°	156.1	33.6
30°-40°	100.8	21.7
40°-50°	22.6	4.9
50°-60°	2.2	0.5
60°-70°	1.1	0.2
70°-80°	0.6	0.1
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	336.5	72.5
0°-40°	437.3	94.2
0°-60°	462.1	99.6
0°-90°	464.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	464.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	505	
5°	483	47
15°	489	134
25°	341	156
35°	163	101
45°	25	23
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1290768

CATALOG NUMBER: P3AS05R60W2N902765DE010 E3CD1MMS_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	505.3
2.5°	497.0
5°	483.4
7.5°	482.7
10°	492.0
12.5°	498.1
15°	488.8
17.5°	460.8
20°	419.9
22.5°	377.2
25°	341.3
27.5°	306.1
30°	264.5
32.5°	215.7
35°	162.9
37.5°	111.3
40°	70.0
42.5°	42.0
45°	24.8
47.5°	14.4
50°	7.5
52.5°	2.5
55°	1.8
57.5°	1.4
60°	1.4
62.5°	1.1
65°	1.1
67.5°	1.1
70°	0.7
72.5°	0.7
75°	0.7
77.5°	0.4
80°	0.4
82.5°	0.4
85°	0.4
87.5°	0.0
90°	0.0

(END OF REPORT)