

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292729

Luminaire Tested: P3AS09R30W2N902765DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292729
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R30W2N902765DE010 E3DL1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 303.0 lumens
Efficiency: N/A
Efficacy: 33.7 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292729
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1292729

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	75	75	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71	71	71	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	69	69	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	63	63	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	176806
5°	168280
10°	141547
15°	102089
20°	63309
25°	36002
30°	20003
35°	10868
40°	5725
45°	3101
50°	1672
55°	1109
60°	1009
65°	1038
70°	898
75°	763
80°	758
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3101 cd/sqm



TEST NUMBER: P1292729

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	22.7
10°-20°	122.4	40.4
20°-30°	70.7	23.3
30°-40°	26.8	8.9
40°-50°	8.2	2.7
50°-60°	2.8	0.9
60°-70°	1.9	0.6
70°-80°	1.0	0.3
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	261.9	86.4
0°-40°	288.8	95.3
0°-60°	299.8	98.9
0°-90°	303.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	303.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	806	
5°	764	69
15°	450	122
25°	149	71
35°	41	27
45°	10	8
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1292729

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	806.3
1°	805.7
2°	800.9
3°	791.7
4°	780.3
5°	764.5
6°	744.5
7°	722.2
8°	697.3
9°	667.5
10°	635.7
11°	601.4
12°	565.0
13°	527.0
14°	488.3
15°	449.7
17.5°	354.6
20°	271.3
22.5°	201.2
25°	148.8
27.5°	108.2
30°	79.0
32.5°	57.0
35°	40.6
37.5°	28.3
40°	20.0
42.5°	14.0
45°	10.0
47.5°	6.9
50°	4.9
52.5°	3.4
55°	2.9
57.5°	2.6
60°	2.3
62.5°	2.0
65°	2.0
67.5°	1.7
70°	1.4
72.5°	1.1
75°	0.9
77.5°	0.9
80°	0.6
82.5°	0.6
85°	0.3
87.5°	0.0



TEST NUMBER: P1292729
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)