

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292774

Luminaire Tested: P3AS09R30W2N902765DE010 E3DLD1H_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292774
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R30W2N902765DE010 E3DLD1H_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 90CRI ,
E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 479.0 lumens
Efficiency: N/A
Efficacy: 53.2 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292774
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLD1H_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1292774

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLD1H_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91				91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83				83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76				76
4	94	85	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70				70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64				64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59				59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55				55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51				51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48				48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45				45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113171
5°	110631
10°	102871
15°	91533
20°	78734
25°	66705
30°	55376
35°	43420
40°	31115
45°	20405
50°	11633
55°	7646
60°	7236
65°	6693
70°	6027
75°	5507
80°	5177
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20405 cd/sqm



TEST NUMBER: P1292774

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLD1H_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.7	9.7
10°-20°	112.1	23.4
20°-30°	126.3	26.4
30°-40°	100.9	21.1
40°-50°	51.8	10.8
50°-60°	19.5	4.1
60°-70°	12.8	2.7
70°-80°	6.9	1.4
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	285.1	59.5
0°-40°	385.9	80.6
0°-60°	457.3	95.5
0°-90°	479.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	479.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	516	
5°	503	47
15°	403	112
25°	276	126
35°	162	101
45°	66	52
55°	20	20
65°	13	13
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1292774

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLD1H_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	516.1
1°	516.1
2°	514.3
3°	511.4
4°	507.3
5°	502.6
6°	496.7
7°	489.0
8°	480.8
9°	471.4
10°	462.0
11°	451.4
12°	440.2
13°	428.5
14°	416.1
15°	403.2
17.5°	370.3
20°	337.4
22.5°	305.6
25°	275.7
27.5°	246.3
30°	218.7
32.5°	190.4
35°	162.2
37.5°	134.6
40°	108.7
42.5°	85.8
45°	65.8
47.5°	48.8
50°	34.1
52.5°	24.1
55°	20.0
57.5°	18.2
60°	16.5
62.5°	14.7
65°	12.9
67.5°	11.2
70°	9.4
72.5°	7.6
75°	6.5
77.5°	5.3
80°	4.1
82.5°	2.9
85°	1.8
87.5°	0.6



TEST NUMBER: P1292774
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLD1H_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)