

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291061

Luminaire Tested: P3AS05R65W2N902750DE010 E3DLP1WMH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291061
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65W2N902750DE010 E3DLP1WMH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 4000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 277.9 lumens
Efficiency: N/A
Efficacy: 47.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291061

CATALOG NUMBER: P3AS05R65W2N902750DE010 E3DLP1WMH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1291061

CATALOG NUMBER: P3AS05R65W2N902750DE010 E3DLP1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	107	101	97	93		104	100	96	92		96	93	90		93	91	88		90	88	86
3	101	94	88	84		99	92	87	83		90	85	82		87	84	81		85	82	79
4	95	87	81	77		93	86	80	76		84	79	75		82	78	74		80	76	73
5	90	81	75	70		88	80	74	70		78	73	69		77	72	69		75	71	68
6	85	76	69	65		84	75	69	65		73	68	64		72	67	64		71	66	63
7	81	71	65	60		79	70	64	60		69	64	60		68	63	59		67	62	59
8	77	67	60	56		75	66	60	56		65	59	56		64	59	55		63	58	55
9	73	63	57	52		72	62	56	52		61	56	52		60	55	52		59	55	52
10	69	59	53	49		68	59	53	49		58	53	49		57	52	49		56	52	49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70652
5°	68897
10°	64172
15°	57503
20°	49658
25°	41301
30°	32587
35°	24146
40°	16631
45°	10327
50°	5595
55°	3517
60°	2982
65°	2698
70°	2308
75°	2033
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 10327 cd/sqm

TEST NUMBER: P1291061

CATALOG NUMBER: P3AS05R65W2N902750DE010 E3DLP1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.1	10.5
10°-20°	70.4	25.3
20°-30°	77.8	28.0
30°-40°	56.5	20.3
40°-50°	26.5	9.5
50°-60°	8.9	3.2
60°-70°	5.1	1.8
70°-80°	2.7	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	177.3	63.8
0°-40°	233.9	84.1
0°-60°	269.2	96.9
0°-90°	277.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	277.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	322	
5°	313	29
15°	253	70
25°	171	78
35°	90	57
45°	33	26
55°	9	9
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1291061

CATALOG NUMBER: P3AS05R65W2N902750DE010 E3DLP1WMH_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	322.2
2.5°	320.2
5°	313.0
7.5°	302.2
10°	288.2
12.5°	271.7
15°	253.3
17.5°	233.3
20°	212.8
22.5°	191.6
25°	170.7
27.5°	149.5
30°	128.7
32.5°	108.6
35°	90.2
37.5°	73.3
40°	58.1
42.5°	44.5
45°	33.3
47.5°	24.0
50°	16.4
52.5°	11.2
55°	9.2
57.5°	8.0
60°	6.8
62.5°	6.0
65°	5.2
67.5°	4.4
70°	3.6
72.5°	3.2
75°	2.4
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)