

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292792

Luminaire Tested: P3AS09R30W2N902765DE010 E3DLD1WH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292792  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R30W2N902765DE010 E3DLD1WH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 90CRI ,  
E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 479.0 lumens  
Efficiency: N/A  
Efficacy: 53.2 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292792  
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLD1WH\_5000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1292792

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLD1WH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	46.7	9.7
10°-20°	112.1	23.4
20°-30°	126.3	26.4
30°-40°	100.9	21.1
40°-50°	51.8	10.8
50°-60°	19.5	4.1
60°-70°	12.8	2.7
70°-80°	6.9	1.4
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	285.1	59.5
0°-40°	385.9	80.6
0°-60°	457.3	95.5
0°-90°	479.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	479.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	516	
5°	503	47
15°	403	112
25°	276	126
35°	162	101
45°	66	52
55°	20	20
65°	13	13
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1292792  
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLD1WH\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	516.1
1°	516.1
2°	514.3
3°	511.4
4°	507.3
5°	502.6
6°	496.7
7°	489.0
8°	480.8
9°	471.4
10°	462.0
11°	451.4
12°	440.2
13°	428.5
14°	416.1
15°	403.2
17.5°	370.3
20°	337.4
22.5°	305.6
25°	275.7
27.5°	246.3
30°	218.7
32.5°	190.4
35°	162.2
37.5°	134.6
40°	108.7
42.5°	85.8
45°	65.8
47.5°	48.8
50°	34.1
52.5°	24.1
55°	20.0
57.5°	18.2
60°	16.5
62.5°	14.7
65°	12.9
67.5°	11.2
70°	9.4
72.5°	7.6
75°	6.5
77.5°	5.3
80°	4.1
82.5°	2.9
85°	1.8
87.5°	0.6



TEST NUMBER: P1292792  
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3DLD1WH\_5000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)