

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292837

Luminaire Tested: P3AS09R30W2N902765DE010 E3PH1MW\_3000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292837  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-4)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R30W2N902765DE010 E3PH1MW\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,  
E3PH1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 600.0 lumens  
Efficiency: N/A  
Efficacy: 66.7 lumens/watt  
Spacing Criteria (0/90/45): 0.33 / 0.33 / 0.34  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292837  
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3PH1MW\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1292837  
 CATALOG NUMBER: P3AS09R30W2N902765DE010 E3PH1MW\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	96	97
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95	97	95	94
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	97	95	94
4	106	101	98	95	105	100	97	95	98	96	94	97	94	92	95	93	91	90	95	93	91
5	104	98	95	92	102	97	94	91	96	93	91	94	92	90	93	91	89	88	93	91	89
6	101	95	92	89	100	95	91	89	94	91	88	92	90	88	91	89	87	86	91	89	87
7	99	93	89	87	98	92	89	86	91	88	86	90	88	86	89	87	85	84	89	87	85
8	96	91	87	84	96	90	87	84	89	86	84	88	86	84	88	85	83	83	88	85	83
9	94	89	85	82	94	88	85	82	87	84	82	87	84	82	86	84	82	81	86	84	82
10	92	87	83	81	92	86	83	81	86	82	80	85	82	80	84	82	80	79	84	82	80

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	854011
5°	746003
10°	409255
15°	188287
20°	101485
25°	34405
30°	4482
35°	669
40°	229
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 0 cd/sqm



TEST NUMBER: P1292837

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3PH1MW\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	271.5	45.3
10°-20°	248.8	41.5
20°-30°	76.5	12.8
30°-40°	2.9	0.5
40°-50°	0.2	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	596.9	99.5
0°-40°	599.8	100.0
0°-60°	600.0	100.0
0°-90°	600.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	600.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3895	
5°	3389	272
15°	829	249
25°	142	77
35°	2	3
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1292837  
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3PH1MW\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3894.6
2.5°	3803.8
5°	3389.1
7.5°	2659.0
10°	1838.0
12.5°	1244.1
15°	829.4
17.5°	581.3
20°	434.9
22.5°	292.7
25°	142.2
27.5°	52.2
30°	17.7
32.5°	5.9
35°	2.5
37.5°	1.7
40°	0.8
42.5°	0.8
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)