

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291071

Luminaire Tested: P3AS05R65W2N902765DE010 E3CB1MMS_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291071
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65W2N902765DE010 E3CB1MMS_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3500K CCT AND, 90CRI ,
E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 497.0 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291071
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3CB1MMS_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1291071
 CATALOG NUMBER: P3AS05R65W2N902765DE010 E3CB1MMS_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87	87	87	87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81	81	81	81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75	75	75	75
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70	70	70	70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58	58	58	58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54	54	54	54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121460
5°	114307
10°	112868
15°	110875
20°	104682
25°	97143
30°	75505
35°	43687
40°	17604
45°	8094
50°	3138
55°	1223
60°	1053
65°	1038
70°	1026
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8094 cd/sqm



TEST NUMBER: P1291071

CATALOG NUMBER: P3AS05R65W2N902765DE010 E3CB1MMS_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.4	9.9
10°-20°	136.4	27.4
20°-30°	178.5	35.9
30°-40°	103.4	20.8
40°-50°	22.1	4.5
50°-60°	3.6	0.7
60°-70°	2.0	0.4
70°-80°	1.2	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.3	73.3
0°-40°	467.7	94.1
0°-60°	493.4	99.3
0°-90°	497.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	497.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	554	
5°	519	49
15°	488	136
25°	402	179
35°	163	103
45°	26	22
55°	3	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1291071
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3CB1MMS_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	553.9
2.5°	538.2
5°	519.3
7.5°	511.7
10°	506.9
12.5°	500.0
15°	488.4
17.5°	470.3
20°	448.6
22.5°	428.1
25°	401.5
27.5°	356.9
30°	298.2
32.5°	231.1
35°	163.2
37.5°	103.3
40°	61.5
42.5°	38.6
45°	26.1
47.5°	16.9
50°	9.2
52.5°	4.4
55°	3.2
57.5°	2.8
60°	2.4
62.5°	2.4
65°	2.0
67.5°	1.6
70°	1.6
72.5°	1.2
75°	1.2
77.5°	0.8
80°	0.8
82.5°	0.4
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)