

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291090

Luminaire Tested: P3AS05R65W2N902765DE010 E3CD1MMS_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291090
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65W2N902765DE010 E3CD1MMS_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 4000K CCT AND, 90CRI ,
E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 497.0 lumens
Efficiency: N/A
Efficacy: 84.2 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291090

CATALOG NUMBER: P3AS05R65W2N902765DE010 E3CD1MMS_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1291090

CATALOG NUMBER: P3AS05R65W2N902765DE010 E3CD1MMS_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	108	106		111	109	106	104		105	103	101		101	99	98		97	96	95
2	108	103	99	96		106	101	98	95		98	95	93		95	93	91		92	90	89
3	103	96	91	87		101	95	90	87		92	88	85		90	87	84		88	85	83
4	97	90	84	80		96	89	84	80		87	82	79		85	81	78		83	80	77
5	93	84	78	74		91	83	78	74		82	77	73		80	76	73		78	75	72
6	88	79	73	69		86	78	73	69		77	72	68		75	71	68		74	70	67
7	84	74	68	64		82	74	68	64		72	67	64		71	67	63		70	66	63
8	80	70	64	60		78	69	64	60		68	63	60		67	63	59		66	62	59
9	76	66	60	56		75	66	60	56		65	60	56		64	59	56		63	59	56
10	72	63	57	53		71	62	57	53		61	56	53		60	56	53		60	55	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121460
5°	114307
10°	112868
15°	110875
20°	104682
25°	97143
30°	75505
35°	43687
40°	17604
45°	8094
50°	3138
55°	1223
60°	1053
65°	1038
70°	1026
75°	1017
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8094 cd/sqm

TEST NUMBER: P1291090

CATALOG NUMBER: P3AS05R65W2N902765DE010 E3CD1MMS_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.4	9.9
10°-20°	136.4	27.4
20°-30°	178.5	35.9
30°-40°	103.4	20.8
40°-50°	22.1	4.5
50°-60°	3.6	0.7
60°-70°	2.0	0.4
70°-80°	1.2	0.2
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.3	73.3
0°-40°	467.7	94.1
0°-60°	493.4	99.3
0°-90°	497.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	497.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	554	
5°	519	49
15°	488	136
25°	402	179
35°	163	103
45°	26	22
55°	3	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1291090

CATALOG NUMBER: P3AS05R65W2N902765DE010 E3CD1MMS_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	553.9
2.5°	538.2
5°	519.3
7.5°	511.7
10°	506.9
12.5°	500.0
15°	488.4
17.5°	470.3
20°	448.6
22.5°	428.1
25°	401.5
27.5°	356.9
30°	298.2
32.5°	231.1
35°	163.2
37.5°	103.3
40°	61.5
42.5°	38.6
45°	26.1
47.5°	16.9
50°	9.2
52.5°	4.4
55°	3.2
57.5°	2.8
60°	2.4
62.5°	2.4
65°	2.0
67.5°	1.6
70°	1.6
72.5°	1.2
75°	1.2
77.5°	0.8
80°	0.8
82.5°	0.4
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)