

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291126

Luminaire Tested: P3AS05R65W2N902765DE010 E3D1WMH_4000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R65W2N902765DE010 E3D1WMH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 4000K CCT AND, 90CRI ,
E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 479.0 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291126
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3D1WMH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1291126

CATALOG NUMBER: P3AS05R65W2N902765DE010 E3D1WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94			94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88			88
3	103	97	92	88	101	95	91	88	93	89	86	90	87	85	88	86	83	82			82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	77			77
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72			72
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67			67
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63			63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59			59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56			56
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128345
5°	119172
10°	115251
15°	111056
20°	102676
25°	93562
30°	72290
35°	41894
40°	16631
45°	7071
50°	1672
55°	229
60°	175
65°	104
70°	128
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7071 cd/sqm



TEST NUMBER: P1291126

CATALOG NUMBER: P3AS05R65W2N902765DE010 E3D1WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.1	10.7
10°-20°	136.3	28.5
20°-30°	172.5	36.0
30°-40°	98.3	20.5
40°-50°	19.5	4.1
50°-60°	1.0	0.2
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	359.9	75.1
0°-40°	458.2	95.7
0°-60°	478.7	99.9
0°-90°	479.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	479.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	585	
5°	541	51
15°	489	136
25°	387	173
35°	156	98
45°	23	20
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1291126
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3D1WMH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	585.3
1°	581.0
2°	571.5
3°	560.5
4°	549.7
5°	541.4
6°	535.3
7°	530.4
8°	526.1
9°	521.7
10°	517.6
11°	513.1
12°	508.3
13°	502.6
14°	496.5
15°	489.2
16°	480.6
17°	471.1
18°	460.9
19°	450.1
20°	440.0
21°	429.8
22°	420.5
23°	410.9
24°	399.7
25°	386.7
26°	371.1
27°	352.4
28°	331.4
29°	308.9
30°	285.5
31°	259.7
32°	234.1
32.5°	220.9
33°	208.1
34°	182.1
35°	156.5
36°	132.9
37°	109.5
37.5°	97.5
38°	87.8
39°	71.1
40°	58.1
42.5°	35.8
45°	22.8



TEST NUMBER: P1291126
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3D1WMH_4000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	13.4
50°	4.9
52.5°	1.0
55°	0.6
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.2
67.5°	0.2
70°	0.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)