

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292899

Luminaire Tested: P3AS09R35W2N902750DE010 E3DL1LI_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292899
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R35W2N902750DE010 E3DL1LI_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI ,
E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 555.0 lumens
Efficiency: N/A
Efficacy: 61.7 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292899
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DL1LI_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1292899

CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DL1LI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.2	20.0
10°-20°	215.5	38.8
20°-30°	141.1	25.4
30°-40°	57.2	10.3
40°-50°	17.2	3.1
50°-60°	5.8	1.1
60°-70°	3.9	0.7
70°-80°	2.3	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	467.7	84.3
0°-40°	525.0	94.6
0°-60°	548.0	98.7
0°-90°	555.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	555.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1276	
5°	1222	111
15°	791	215
25°	300	141
35°	87	57
45°	21	17
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1292899
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DL1LI_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1276.5
1°	1274.4
2°	1268.6
3°	1257.0
4°	1243.3
5°	1222.2
6°	1195.8
7°	1166.2
8°	1132.9
9°	1094.9
10°	1052.7
11°	1005.7
12°	956.6
13°	901.7
14°	849.4
15°	790.8
17.5°	648.8
20°	514.7
22.5°	395.9
25°	300.4
27.5°	223.8
30°	164.7
32.5°	120.9
35°	87.1
37.5°	61.8
40°	43.3
42.5°	30.1
45°	20.6
47.5°	13.7
50°	9.0
52.5°	6.9
55°	6.3
57.5°	5.8
60°	5.3
62.5°	4.8
65°	3.7
67.5°	3.2
70°	3.2
72.5°	2.6
75°	2.1
77.5°	1.6
80°	1.6
82.5°	1.1
85°	0.5
87.5°	0.5



TEST NUMBER: P1292899
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DL1LI_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)