

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292920

Luminaire Tested: P3AS09R35W2N902750DE010 E3DLD1GPH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292920  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R35W2N902750DE010 E3DLD1GPH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 231.0 lumens  
Efficiency: N/A  
Efficacy: 25.7 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292920  
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DLD1GPH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1292920  
 CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DLD1GPH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	52759
5°	51640
10°	48362
15°	43428
20°	37780
25°	32179
30°	26966
35°	21469
40°	15515
45°	9830
50°	5356
55°	3708
60°	3508
65°	3269
70°	3142
75°	2626
80°	2526
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9830 cd/sqm



TEST NUMBER: P1292920

CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DLD1GPH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	21.8	9.5
10°-20°	53.2	23.0
20°-30°	61.0	26.4
30°-40°	49.8	21.5
40°-50°	25.1	10.9
50°-60°	9.3	4.0
60°-70°	6.2	2.7
70°-80°	3.5	1.5
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	136.1	58.9
0°-40°	185.8	80.4
0°-60°	220.2	95.3
0°-90°	231.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	231.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	241	
5°	235	22
15°	191	53
25°	133	61
35°	80	50
45°	32	25
55°	10	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1292920  
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DLD1GPH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	240.6
1°	240.4
2°	239.8
3°	238.6
4°	236.9
5°	234.6
6°	231.8
7°	228.9
8°	225.2
9°	221.5
10°	217.2
11°	212.7
12°	207.8
13°	202.4
14°	196.7
15°	191.3
17.5°	176.7
20°	161.9
22.5°	146.7
25°	133.0
27.5°	119.6
30°	106.5
32.5°	93.3
35°	80.2
37.5°	67.1
40°	54.2
42.5°	42.2
45°	31.7
47.5°	22.8
50°	15.7
52.5°	11.4
55°	9.7
57.5°	8.8
60°	8.0
62.5°	7.1
65°	6.3
67.5°	5.4
70°	4.9
72.5°	4.0
75°	3.1
77.5°	2.6
80°	2.0
82.5°	1.4
85°	0.9
87.5°	0.6



TEST NUMBER: P1292920  
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DLD1GPH\_3000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)