

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292973

Luminaire Tested: P3AS09R35W2N902750DE010 E3DLP1WH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1292973  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R35W2N902750DE010 E3DLP1WH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 90CRI ,  
E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 618.0 lumens  
Efficiency: N/A  
Efficacy: 68.7 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1292973  
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DLP1WH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1292973  
 CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DLP1WH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 114 | 112 | 109 | 107 | 112 | 109 | 107 | 106 | 105 | 104 | 102 | 102 | 100 | 99  | 98  | 97  | 96  | 96  | 96  | 96  | 95  |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  | 97  | 95  | 93  | 94  | 93  | 91  | 91  | 91  | 91  | 90  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 92  | 89  | 93  | 90  | 88  | 91  | 88  | 86  | 86  | 86  | 86  | 85  |
| 4   | 100 | 94  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 84  | 89  | 85  | 83  | 87  | 84  | 82  | 82  | 82  | 82  | 80  |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 83  | 80  | 86  | 82  | 79  | 85  | 81  | 78  | 83  | 80  | 78  | 78  | 78  | 78  | 76  |
| 6   | 92  | 85  | 80  | 76  | 91  | 84  | 79  | 76  | 83  | 78  | 75  | 81  | 77  | 75  | 80  | 77  | 74  | 74  | 74  | 74  | 73  |
| 7   | 89  | 81  | 76  | 72  | 88  | 80  | 75  | 72  | 79  | 75  | 71  | 78  | 74  | 71  | 77  | 73  | 71  | 71  | 71  | 71  | 70  |
| 8   | 85  | 77  | 72  | 69  | 84  | 77  | 72  | 68  | 76  | 71  | 68  | 75  | 71  | 68  | 74  | 70  | 68  | 68  | 68  | 68  | 66  |
| 9   | 82  | 74  | 69  | 66  | 81  | 74  | 69  | 65  | 73  | 68  | 65  | 72  | 68  | 65  | 71  | 67  | 65  | 65  | 65  | 65  | 64  |
| 10  | 79  | 71  | 66  | 63  | 78  | 71  | 66  | 63  | 70  | 66  | 63  | 69  | 65  | 62  | 69  | 65  | 62  | 62  | 62  | 62  | 61  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 311686 |
| 5°  | 299559 |
| 10° | 261006 |
| 15° | 199910 |
| 20° | 133758 |
| 25° | 80932  |
| 30° | 46438  |
| 35° | 25966  |
| 40° | 13797  |
| 45° | 7102   |
| 50° | 3411   |
| 55° | 2714   |
| 60° | 2588   |
| 65° | 2127   |
| 70° | 2244   |
| 75° | 2033   |
| 80° | 2273   |
| 85° | 1510   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7102 cd/sqm



TEST NUMBER: P1292973

CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DLP1WH\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 123.8  | 20.0      |
| 10°-20°   | 240.0  | 38.8      |
| 20°-30°   | 157.1  | 25.4      |
| 30°-40°   | 63.7   | 10.3      |
| 40°-50°   | 19.1   | 3.1       |
| 50°-60°   | 6.5    | 1.1       |
| 60°-70°   | 4.3    | 0.7       |
| 70°-80°   | 2.6    | 0.4       |
| 80°-90°   | 0.9    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 520.9  | 84.3      |
| 0°-40°    | 584.6  | 94.6      |
| 0°-60°    | 610.2  | 98.7      |
| 0°-90°    | 618.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 618.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1421 |      |
| 5°  | 1361 | 124  |
| 15° | 881  | 240  |
| 25° | 334  | 157  |
| 35° | 97   | 64   |
| 45° | 23   | 19   |
| 55° | 7    | 7    |
| 65° | 4    | 4    |
| 75° | 2    | 3    |
| 85° | 1    | 1    |
| 90° | 0    |      |



TEST NUMBER: P1292973  
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DLP1WH\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1421.4 |
| 1°    | 1419.1 |
| 2°    | 1412.6 |
| 3°    | 1399.7 |
| 4°    | 1384.4 |
| 5°    | 1360.9 |
| 6°    | 1331.5 |
| 7°    | 1298.6 |
| 8°    | 1261.5 |
| 9°    | 1219.2 |
| 10°   | 1172.2 |
| 11°   | 1119.9 |
| 12°   | 1065.2 |
| 13°   | 1004.1 |
| 14°   | 945.9  |
| 15°   | 880.6  |
| 17.5° | 722.5  |
| 20°   | 573.2  |
| 22.5° | 440.9  |
| 25°   | 334.5  |
| 27.5° | 249.3  |
| 30°   | 183.4  |
| 32.5° | 134.6  |
| 35°   | 97.0   |
| 37.5° | 68.8   |
| 40°   | 48.2   |
| 42.5° | 33.5   |
| 45°   | 22.9   |
| 47.5° | 15.3   |
| 50°   | 10.0   |
| 52.5° | 7.6    |
| 55°   | 7.1    |
| 57.5° | 6.5    |
| 60°   | 5.9    |
| 62.5° | 5.3    |
| 65°   | 4.1    |
| 67.5° | 3.5    |
| 70°   | 3.5    |
| 72.5° | 2.9    |
| 75°   | 2.4    |
| 77.5° | 1.8    |
| 80°   | 1.8    |
| 82.5° | 1.2    |
| 85°   | 0.6    |
| 87.5° | 0.6    |



TEST NUMBER: P1292973  
CATALOG NUMBER: P3AS09R35W2N902750DE010 E3DLP1WH\_5000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)