

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293029

Luminaire Tested: P3AS09R35W2N902765DE010 E3CD1MW_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293029
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R35W2N902765DE010 E3CD1MW_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 6500K CCT AND, 90CRI ,
E3CD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 747.1 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293029
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3CD1MW_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1293029

CATALOG NUMBER: P3AS09R35W2N902765DE010 E3CD1MW_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	98	98	98	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	94	94	94	93
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	94	92	90	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	91	89	87	86
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	89	86	84	83
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	86	83	81	80
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	84	81	79	77
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	81	78	76	75
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	79	76	74	73
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	77	74	71	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	487088
5°	477172
10°	443924
15°	325450
20°	166661
25°	60076
30°	23396
35°	8191
40°	3378
45°	899
50°	819
55°	918
60°	789
65°	623
70°	769
75°	1017
80°	758
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 1017 cd/sqm



TEST NUMBER: P1293029

CATALOG NUMBER: P3AS09R35W2N902765DE010 E3CD1MW_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.1	27.1
10°-20°	379.2	50.8
20°-30°	134.2	18.0
30°-40°	23.5	3.1
40°-50°	3.5	0.5
50°-60°	1.9	0.3
60°-70°	1.4	0.2
70°-80°	1.0	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	715.5	95.8
0°-40°	739.0	98.9
0°-60°	744.4	99.6
0°-90°	747.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	747.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2221	
5°	2168	202
15°	1434	379
25°	248	134
35°	31	24
45°	3	3
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1293029

CATALOG NUMBER: P3AS09R35W2N902765DE010 E3CD1MW_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2221.3
1°	2220.7
2°	2213.7
3°	2200.1
4°	2187.8
5°	2167.8
6°	2147.2
7°	2124.3
8°	2096.0
9°	2051.9
10°	1993.7
11°	1913.1
12°	1816.0
13°	1700.7
14°	1573.6
15°	1433.6
17.5°	1067.7
20°	714.2
22.5°	430.6
25°	248.3
27.5°	148.2
30°	92.4
32.5°	53.5
35°	30.6
37.5°	19.4
40°	11.8
42.5°	5.9
45°	2.9
47.5°	2.4
50°	2.4
52.5°	2.4
55°	2.4
57.5°	1.8
60°	1.8
62.5°	1.8
65°	1.2
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.0
87.5°	0.0



TEST NUMBER: P1293029
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3CD1MW_6500K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)