

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293076

Luminaire Tested: P3AS09R35W2N902765DE010 E3DLD1GPH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293076  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R35W2N902765DE010 E3DLD1GPH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 233.0 lumens  
Efficiency: N/A  
Efficacy: 25.9 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293076  
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLD1GPH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293076

CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLD1GPH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |   |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |   |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |   |
| 1   | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99  | 99  | 98  | 96  | 96  | 94  | 93  | 91  |    |    |   |
| 2   | 106 | 100 | 96  | 92  | 104 | 98  | 94  | 91  | 95  | 92  | 89  | 92  | 89  | 87  | 89  | 87  | 85  | 83  |    |    |   |
| 3   | 100 | 92  | 87  | 82  | 98  | 91  | 86  | 81  | 88  | 84  | 80  | 86  | 82  | 79  | 83  | 80  | 78  | 76  |    |    |   |
| 4   | 94  | 85  | 79  | 74  | 92  | 84  | 78  | 74  | 82  | 77  | 73  | 80  | 75  | 72  | 78  | 74  | 71  | 69  |    |    |   |
| 5   | 89  | 79  | 73  | 68  | 87  | 78  | 72  | 67  | 76  | 71  | 67  | 75  | 70  | 66  | 73  | 69  | 66  | 64  |    |    |   |
| 6   | 84  | 74  | 67  | 62  | 82  | 73  | 67  | 62  | 71  | 66  | 61  | 70  | 65  | 61  | 68  | 64  | 61  | 59  |    |    |   |
| 7   | 79  | 69  | 62  | 57  | 78  | 68  | 62  | 57  | 67  | 61  | 57  | 65  | 60  | 57  | 64  | 60  | 56  | 55  |    |    |   |
| 8   | 75  | 64  | 58  | 53  | 74  | 64  | 57  | 53  | 63  | 57  | 53  | 62  | 56  | 53  | 61  | 56  | 52  | 51  |    |    |   |
| 9   | 71  | 60  | 54  | 50  | 70  | 60  | 54  | 50  | 59  | 53  | 49  | 58  | 53  | 49  | 57  | 52  | 49  | 48  |    |    |   |
| 10  | 67  | 57  | 51  | 46  | 66  | 56  | 50  | 46  | 56  | 50  | 46  | 55  | 50  | 46  | 54  | 49  | 46  | 45  |    |    |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 53219 |
| 5°  | 52102 |
| 10° | 48786 |
| 15° | 43791 |
| 20° | 38107 |
| 25° | 32470 |
| 30° | 27194 |
| 35° | 21656 |
| 40° | 15658 |
| 45° | 9924  |
| 50° | 5390  |
| 55° | 3747  |
| 60° | 3552  |
| 65° | 3269  |
| 70° | 3142  |
| 75° | 2711  |
| 80° | 2526  |
| 85° | 2264  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9924 cd/sqm



TEST NUMBER: P1293076

CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLD1GPH\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 22.0   | 9.5       |
| 10°-20°   | 53.7   | 23.0      |
| 20°-30°   | 61.5   | 26.4      |
| 30°-40°   | 50.2   | 21.6      |
| 40°-50°   | 25.3   | 10.9      |
| 50°-60°   | 9.4    | 4.0       |
| 60°-70°   | 6.3    | 2.7       |
| 70°-80°   | 3.5    | 1.5       |
| 80°-90°   | 1.1    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 137.2  | 58.9      |
| 0°-40°    | 187.4  | 80.4      |
| 0°-60°    | 222.1  | 95.3      |
| 0°-90°    | 233.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 233.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 243 |      |
| 5°  | 237 | 22   |
| 15° | 193 | 54   |
| 25° | 134 | 62   |
| 35° | 81  | 50   |
| 45° | 32  | 25   |
| 55° | 10  | 9    |
| 65° | 6   | 6    |
| 75° | 3   | 3    |
| 85° | 1   | 1    |
| 90° | 0   |      |



TEST NUMBER: P1293076  
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLD1GPH\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 242.7 |
| 1°    | 242.4 |
| 2°    | 241.9 |
| 3°    | 240.7 |
| 4°    | 239.0 |
| 5°    | 236.7 |
| 6°    | 233.8 |
| 7°    | 230.9 |
| 8°    | 227.2 |
| 9°    | 223.4 |
| 10°   | 219.1 |
| 11°   | 214.5 |
| 12°   | 209.6 |
| 13°   | 204.1 |
| 14°   | 198.4 |
| 15°   | 192.9 |
| 17.5° | 178.2 |
| 20°   | 163.3 |
| 22.5° | 148.0 |
| 25°   | 134.2 |
| 27.5° | 120.6 |
| 30°   | 107.4 |
| 32.5° | 94.2  |
| 35°   | 80.9  |
| 37.5° | 67.7  |
| 40°   | 54.7  |
| 42.5° | 42.6  |
| 45°   | 32.0  |
| 47.5° | 23.0  |
| 50°   | 15.8  |
| 52.5° | 11.5  |
| 55°   | 9.8   |
| 57.5° | 8.9   |
| 60°   | 8.1   |
| 62.5° | 7.2   |
| 65°   | 6.3   |
| 67.5° | 5.5   |
| 70°   | 4.9   |
| 72.5° | 4.0   |
| 75°   | 3.2   |
| 77.5° | 2.6   |
| 80°   | 2.0   |
| 82.5° | 1.4   |
| 85°   | 0.9   |
| 87.5° | 0.6   |



TEST NUMBER: P1293076  
CATALOG NUMBER: P3AS09R35W2N902765DE010 E3DLD1GPH\_5000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)