

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291337

Luminaire Tested: P3AS05R70W2N902750DE010 E3DLP1MW\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1291337  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R70W2N902750DE010 E3DLP1MW\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 2700K CCT AND, 90CRI ,  
E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 258.0 lumens  
Efficiency: N/A  
Efficacy: 43.7 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1291337  
CATALOG NUMBER: P3AS05R70W2N902750DE010 E3DLP1MW\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1291337  
 CATALOG NUMBER: P3AS05R70W2N902750DE010 E3DLP1MW\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    | 100 |
| 1   | 113 | 110 | 107 | 104 | 110 | 107 | 105 | 103 | 103 | 101 | 100 | 100 | 98  | 97  | 96  | 95  | 94  | 92  |    |    | 92  |
| 2   | 106 | 101 | 97  | 93  | 104 | 99  | 95  | 92  | 96  | 93  | 90  | 93  | 90  | 88  | 90  | 88  | 86  | 84  |    |    | 84  |
| 3   | 100 | 93  | 88  | 83  | 98  | 92  | 87  | 83  | 89  | 85  | 81  | 87  | 83  | 80  | 84  | 81  | 79  | 77  |    |    | 77  |
| 4   | 95  | 86  | 80  | 76  | 93  | 85  | 80  | 75  | 83  | 78  | 74  | 81  | 77  | 73  | 79  | 76  | 73  | 71  |    |    | 71  |
| 5   | 89  | 80  | 74  | 69  | 88  | 79  | 73  | 69  | 78  | 72  | 68  | 76  | 71  | 68  | 74  | 70  | 67  | 65  |    |    | 65  |
| 6   | 85  | 75  | 68  | 64  | 83  | 74  | 68  | 64  | 73  | 67  | 63  | 71  | 66  | 63  | 70  | 65  | 62  | 61  |    |    | 61  |
| 7   | 80  | 70  | 64  | 59  | 79  | 69  | 63  | 59  | 68  | 62  | 58  | 67  | 62  | 58  | 66  | 61  | 58  | 56  |    |    | 56  |
| 8   | 76  | 66  | 59  | 55  | 75  | 65  | 59  | 55  | 64  | 58  | 54  | 63  | 58  | 54  | 62  | 57  | 54  | 52  |    |    | 52  |
| 9   | 72  | 62  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 55  | 51  | 59  | 54  | 51  | 58  | 54  | 50  | 49  |    |    | 49  |
| 10  | 69  | 58  | 52  | 48  | 67  | 58  | 52  | 48  | 57  | 51  | 48  | 56  | 51  | 48  | 55  | 51  | 47  | 46  |    |    | 46  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 60521 |
| 5°  | 59410 |
| 10° | 56022 |
| 15° | 50829 |
| 20° | 44477 |
| 25° | 37502 |
| 30° | 30714 |
| 35° | 23825 |
| 40° | 17061 |
| 45° | 10792 |
| 50° | 5390  |
| 55° | 3288  |
| 60° | 2851  |
| 65° | 2594  |
| 70° | 2308  |
| 75° | 2118  |
| 80° | 1768  |
| 85° | 1761  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10792 cd/sqm



TEST NUMBER: P1291337

CATALOG NUMBER: P3AS05R70W2N902750DE010 E3DLP1MW\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 25.2   | 9.8       |
| 10°-20°   | 62.3   | 24.2      |
| 20°-30°   | 71.0   | 27.5      |
| 30°-40°   | 55.5   | 21.5      |
| 40°-50°   | 27.3   | 10.6      |
| 50°-60°   | 8.4    | 3.2       |
| 60°-70°   | 5.0    | 1.9       |
| 70°-80°   | 2.7    | 1.0       |
| 80°-90°   | 0.8    | 0.3       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 158.5  | 61.4      |
| 0°-40°    | 213.9  | 82.9      |
| 0°-60°    | 249.6  | 96.7      |
| 0°-90°    | 258.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 258.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 276 |      |
| 5°  | 270 | 25   |
| 15° | 224 | 62   |
| 25° | 155 | 71   |
| 35° | 89  | 55   |
| 45° | 35  | 27   |
| 55° | 9   | 8    |
| 65° | 5   | 5    |
| 75° | 2   | 3    |
| 85° | 1   | 1    |
| 90° | 0   |      |



TEST NUMBER: P1291337  
CATALOG NUMBER: P3AS05R70W2N902750DE010 E3DLP1MW\_2700K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 276.0 |
| 2.5°  | 274.5 |
| 5°    | 269.9 |
| 7.5°  | 262.3 |
| 10°   | 251.6 |
| 12.5° | 239.0 |
| 15°   | 223.9 |
| 17.5° | 207.8 |
| 20°   | 190.6 |
| 22.5° | 172.6 |
| 25°   | 155.0 |
| 27.5° | 137.8 |
| 30°   | 121.3 |
| 32.5° | 104.8 |
| 35°   | 89.0  |
| 37.5° | 73.9  |
| 40°   | 59.6  |
| 42.5° | 46.3  |
| 45°   | 34.8  |
| 47.5° | 24.4  |
| 50°   | 15.8  |
| 52.5° | 10.4  |
| 55°   | 8.6   |
| 57.5° | 7.5   |
| 60°   | 6.5   |
| 62.5° | 5.7   |
| 65°   | 5.0   |
| 67.5° | 4.3   |
| 70°   | 3.6   |
| 72.5° | 2.9   |
| 75°   | 2.5   |
| 77.5° | 2.2   |
| 80°   | 1.4   |
| 82.5° | 1.1   |
| 85°   | 0.7   |
| 87.5° | 0.4   |
| 90°   | 0.0   |

(END OF REPORT)