

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293208

Luminaire Tested: P3AS09R40W2N902750DE010 E3D1WH_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293208
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40W2N902750DE010 E3D1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 816.0 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293208
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3D1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1293208
 CATALOG NUMBER: P3AS09R40W2N902750DE010 E3D1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96		
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92		
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	93	91	90	88		
4	103	97	93	90	101	96	92	89	94	91	88	92	89	87	90	88	86	85		
5	99	93	89	85	98	92	88	85	91	87	84	89	86	84	88	85	83	82		
6	96	89	85	81	95	89	84	81	87	83	81	86	83	80	85	82	80	79		
7	93	86	81	78	92	85	81	78	84	80	77	83	80	77	82	79	77	76		
8	90	83	78	75	89	82	78	75	81	77	75	80	77	74	79	76	74	73		
9	87	80	75	72	86	79	75	72	78	75	72	78	74	72	77	74	71	70		
10	84	77	72	70	83	77	72	69	76	72	69	75	72	69	74	71	69	68		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	415932
5°	412942
10°	402130
15°	359208
20°	238184
25°	89231
30°	23877
35°	9342
40°	3349
45°	1582
50°	478
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1582 cd/sqm



TEST NUMBER: P1293208

CATALOG NUMBER: P3AS09R40W2N902750DE010 E3D1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	177.0	21.7
10°-20°	419.3	51.4
20°-30°	190.1	23.3
30°-40°	24.6	3.0
40°-50°	4.2	0.5
50°-60°	0.5	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	786.4	96.4
0°-40°	811.1	99.4
0°-60°	815.8	100.0
0°-90°	816.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	816.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1897	
5°	1876	177
15°	1582	419
25°	369	190
35°	35	25
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1293208
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3D1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1896.8
1°	1895.7
2°	1892.8
3°	1888.5
4°	1883.1
5°	1876.0
6°	1867.7
7°	1857.4
8°	1844.8
9°	1827.7
10°	1806.0
11°	1780.5
12°	1746.6
13°	1704.6
14°	1649.7
15°	1582.3
16°	1496.3
17°	1398.3
18°	1280.6
19°	1156.4
20°	1020.7
21°	885.0
22°	751.3
23°	618.2
24°	487.3
25°	368.8
26°	273.1
27°	200.0
28°	150.3
29°	116.8
30°	94.3
31°	78.0
32°	65.1
32.5°	59.4
33°	53.7
34°	43.7
35°	34.9
36°	27.4
37°	21.7
37.5°	19.4
38°	17.1
39°	14.3
40°	11.7
42.5°	7.7
45°	5.1



TEST NUMBER: P1293208
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3D1WH_3000K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	3.1
50°	1.4
52.5°	0.6
55°	0.6
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)