

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293225

Luminaire Tested: P3AS09R40W2N902750DE010 E3DL1H_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293225
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40W2N902750DE010 E3DL1H_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 4000K CCT AND, 90CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 689.0 lumens
Efficiency: N/A
Efficacy: 76.6 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293225
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DL1H_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1293225

CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DL1H_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	124.0	18.0
10°-20°	266.2	38.6
20°-30°	190.0	27.6
30°-40°	69.9	10.1
40°-50°	22.0	3.2
50°-60°	7.7	1.1
60°-70°	5.2	0.8
70°-80°	3.1	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	580.1	84.2
0°-40°	650.0	94.3
0°-60°	679.7	98.7
0°-90°	689.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	689.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1390	
5°	1345	124
15°	978	266
25°	409	190
35°	104	70
45°	27	22
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1293225
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DL1H_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1390.4
2.5°	1379.7
5°	1344.8
7.5°	1286.9
10°	1206.4
12.5°	1104.1
15°	977.6
17.5°	835.6
20°	686.0
22.5°	538.8
25°	409.2
27.5°	300.4
30°	211.7
32.5°	148.4
35°	103.5
37.5°	73.3
40°	52.6
42.5°	37.8
45°	27.2
47.5°	18.3
50°	12.4
52.5°	8.9
55°	8.3
57.5°	7.7
60°	6.5
62.5°	5.9
65°	5.3
67.5°	4.7
70°	4.1
72.5°	3.5
75°	3.0
77.5°	2.4
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)