

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291433

Luminaire Tested: P3AS05R70W2N902765DE010 E3DL1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291433
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R70W2N902765DE010 E3DL1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 6500K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 197.0 lumens
Efficiency: N/A
Efficacy: 33.4 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291433
CATALOG NUMBER: P3AS05R70W2N902765DE010 E3DL1GPH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1291433

CATALOG NUMBER: P3AS05R70W2N902765DE010 E3DL1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.1	8.2
10°-20°	43.2	21.9
20°-30°	56.1	28.5
30°-40°	47.6	24.2
40°-50°	24.6	12.5
50°-60°	4.7	2.4
60°-70°	2.5	1.3
70°-80°	1.6	0.8
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	115.5	58.6
0°-40°	163.1	82.8
0°-60°	192.4	97.7
0°-90°	197.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	197.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	174	
5°	171	16
15°	154	43
25°	123	56
35°	77	48
45°	32	25
55°	4	5
65°	2	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1291433
CATALOG NUMBER: P3AS05R70W2N902765DE010 E3DL1GPH_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	173.9
2.5°	173.3
5°	171.2
7.5°	168.1
10°	164.3
12.5°	159.6
15°	154.4
17.5°	147.9
20°	140.7
22.5°	132.4
25°	123.3
27.5°	112.9
30°	101.7
32.5°	89.4
35°	76.7
37.5°	64.2
40°	52.2
42.5°	41.1
45°	31.7
47.5°	23.3
50°	13.5
52.5°	5.9
55°	3.7
57.5°	3.5
60°	3.1
62.5°	2.9
65°	2.5
67.5°	2.3
70°	2.0
72.5°	1.8
75°	1.6
77.5°	1.2
80°	1.0
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)