

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293250

Luminaire Tested: P3AS09R40W2N902750DE010 E3DLD1GPH\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293250  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R40W2N902750DE010 E3DLD1GPH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 4000K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 259.0 lumens  
Efficiency: N/A  
Efficacy: 28.8 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293250  
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLD1GPH\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1293250  
 CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLD1GPH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	58131
5°	57077
10°	53818
15°	48877
20°	42937
25°	36655
30°	30384
35°	23423
40°	16660
45°	11226
50°	6141
55°	4320
60°	4079
65°	3736
70°	3334
75°	3219
80°	2526
85°	2264

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11226 cd/sqm



TEST NUMBER: P1293250

CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLD1GPH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	24.2	9.3
10°-20°	60.0	23.2
20°-30°	69.3	26.8
30°-40°	54.6	21.1
40°-50°	28.1	10.8
50°-60°	10.7	4.1
60°-70°	7.1	2.7
70°-80°	3.8	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	153.5	59.3
0°-40°	208.1	80.4
0°-60°	246.9	95.3
0°-90°	259.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	259.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	265	
5°	259	24
15°	215	60
25°	152	69
35°	88	55
45°	36	28
55°	11	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1293250  
CATALOG NUMBER: P3AS09R40W2N902750DE010 E3DLD1GPH\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	265.1
2.5°	263.7
5°	259.3
7.5°	251.8
10°	241.7
12.5°	229.8
15°	215.3
17.5°	200.2
20°	184.0
22.5°	167.5
25°	151.5
27.5°	135.6
30°	120.0
32.5°	104.0
35°	87.5
37.5°	72.2
40°	58.2
42.5°	46.4
45°	36.2
47.5°	26.4
50°	18.0
52.5°	13.0
55°	11.3
57.5°	10.1
60°	9.3
62.5°	8.1
65°	7.2
67.5°	6.1
70°	5.2
72.5°	4.3
75°	3.8
77.5°	2.9
80°	2.0
82.5°	1.7
85°	0.9
87.5°	0.6
90°	0.0

(END OF REPORT)